

CSA & DESIGN — 1418750

Application number

1418750

Registration number

TMA830597

Type(s)

Design

Category

Certification Mark

CIPO Status

REGISTERED

TM5 status

LIVE/REGISTRATION/Issued
and Active



The trademark application has
been registered with the Office.

Filed

2008-11-10

Registered

2012-08-24

Registration Expiry Date

2027-08-24

Registered Owner

CANADIAN STANDARDS
ASSOCIATION
178 Rexdale Blvd.
Toronto
ONTARIO M9W1R3

Agent

BAKER & MCKENZIE LLP
BROOKFIELD PLACE
181 BAY STREET, SUITE
2100
P.O. BOX 874
TORONTO
ONTARIO M5J2T3

Documents

[View documents](#)

Index headings

CSA

Vienna information (Code & Description)

27.1.1	Letters or numerals forming geometrical figures, written or typographical matter in perspective
A 27.1.6	Letters or numerals forming a circle or a circumference
27.5.1	Letters presenting a special form of writing
A 27.5.5	Letters containing written or typographical matter
A 27.5.22	Monograms formed of intertwined, overlapping or otherwise combined letters

Goods (Nice class & Statement)

(1) Electronic business equipment, namely, accessory telephones, adding machines, addressing machines, binding machines, cash registers, collators, convertors, dictating and transcribing machines, disk drives, display terminals, folding machines, hole punching machines, labeling and addressing machines, pencil sharpeners, power units, projectors, punches, recorders, sorters, stackers, staplers, stitchers, tape readers, televisions, typewriters; wires, namely, cord sets, splicing wire connectors, adapter boxes; air compressors; airport lighting cables; attachment plugs, battery chargers, surge suppression; bactericidal lamps; bottling machines; boxes namely cutout, junction and pull boxes; brooders; canning machines; capacitors; carbonators; arc fault circuit interrupters, modification centers, molded case type; cleaning machines namely high pressure, vacuum cleaners; air cleaners, air conditioners, air handling units, apparatus, combination units, components, parts and subassemblies; heaters, heating appliances and heating equipment, namely, water heaters; heat pumps; conveyors; cranes and hoists; dairy machines; dental equipment namely, dental chairs; display turntables; door operating units; dry cleaning equipment; electrical controls; electric discharge lamp control equipment; electrical metallic tubing; electronic scales; elevator and escalator equipment namely door locking devices and contacts, elevating devices, elevator and escalator electrical equipment, braking systems, hydraulic control valves, magnetic motor controllers, oil buffers; fire alarm and signal cables; food-preparing machines; fuel burning equipment namely gas burners, electrical equipment; fuels handling equipment namely petroleum fuels containers; fuseholder assemblies; fuseholder rosettes; fuses namely cartridge, low voltage, high rupturing capacity, miniature, plug, special, supplemental; garbage disposal units; generators namely carbon dioxide gas, ozone gas, hydrogen, water electrolysis; ground fault devices namely interrupters, detectors, and protectors; hose assemblies namely composite materials, elastomeric, thermoplastic or flexible metallic hose; incubators; industrial control equipment namely air conditioners, refrigerators, milk coolers; household and commercial appliances, namely, carbonators, floor polishers, floor scrubbers, slicing machines, stitchers; miscellaneous apparatus namely, attachment plugs, blood pressure measuring apparatus, carbonators, cultivators, panelboards, polishers, switchgear assemblies; motor controllers namely, panelboards; programmable controllers namely, electric fence controllers; industrial control assemblies namely, panelboards, switches, switchgear assemblies namely, switches; insulating devices and materials namely bushings, transformers, motor insulation, electrical tape, miscellaneous, supports; labeling machines; laboratory equipment namely components, electrical, water baths; lamps namely auxiliaries, filament, mercury, metal-halide, high pressure sodium, fluorescent, self-ballasted adapters, integral-ballasted adapters, incandescent, led; lighting namely, lampholders; liquid pumps namely aquarium,

circulating, component, water quality; portable lights, filaments, floodlights, exit type lights, light fixtures, gas-tube lights, light hangers, lighting poles, light fittings, fittings for lights, enclosed lights, gasket lights, incandescent lights, track lighting, light components, surface mounted lights, light kits, hand lamps, nightlight, street and road lights, tungsten halogen lights; medical electrical equipment namely gamma beam therapy, microwave therapy, nerve and muscle stimulators, radiation detectors, dosimeters, x-ray, lung ventilators, haemodialysis, haemodiafiltration, partial pressure monitoring, infusion pumps, electromyographs, operating tables; oil burner; photo printing equipment; packaging equipment; paint sprayers; picture machines and appliances namely professional, non-professional, stereopticon; printing and paper processing equipment; process control equipment; raceways, wireways and busways; radio appliances namely transmitters and receivers; receptacles; rectifiers namely power supplies; refrigeration equipment; service mast components; sewing machines; signal appliances namely fire alarm equipment; signs namely portable displays, stationary, sprayers namely paint, heaters, miscellaneous, stitchers; switches namely selector, solid state, snap, lighting control; telecommunications equipment namely telephones; transformers; transmitters and receivers namely amateur, commercial and communication; valves namely actuators, electrical; vending machines; welding machines; wire connecting devices namely quick-connect terminals, terminal assemblies; electrical equipment accessories namely, amplifiers, preamplifiers, circuit breakers, conduit and fittings, fuses, transformers, cable connectors, wire connectors; motor operated appliances namely, air compressors; motorized components for hygiene and cosmetic appliances namely, shaving and massage appliances; protective devices namely, circuit breakers; pressurized equipment namely, air compressors

(2) Boilers namely steam, hot water; fuel burning equipment namely appliances, boilers, burners, furnaces; heaters and comfort conditioning equipment; solid fuel burning equipment namely boilers, furnaces, ranges, room heaters; water heaters, Comfort conditioning equipment accessories, namely, boilers

(3) Building products and materials namely roof and floor trusses; factory constructed buildings and structures namely mobile units, commercial units, industrial units, modular homes, trailers, recreational vehicles

(4) Building products and materials namely sliding doors, windows; cleaning machines namely vacuum cleaners, washing machines; clock type switches; components of cord sets; control cables; cord sets namely cord-sets for power supply, extension cords, heater cords; electric fence controllers and energizers; fuel burning equipment; sediment traps; heater elements; heater namely irons, sauna, warming pads, lampholders namely electric discharge, fittings; heaters namely hair dressing, hand drying; machine tools; metal and non-metallic conduits; outlet boxes and fittings; panelboards; plates and covers; power cables; refrigerators namely absorption type,

compression type, thermoelectric type; switches namely air break, automatic, components, dead-front and enclosed, electronic, enclosed single-pole air, high voltage, magnetic type, pressure type; switchboard; thermal spillage; time indicating and recording appliances namely clocks; water heaters; woodworking machinery

(5) Pipe and pipe fittings namely asbestos cement, cast iron, drains and cleanouts, frames and covers, leads, mechanical coupling, mechanical joints, non-transition joints; plastic pipe namely abs blending resins, abs compounds, chlorinated polyvinylchloride, drain and sewer fittings, flexible pressure pipe, gas piping systems, laboratory drainage, polyamide compounds, polyethylene, polybutylene, polypropylene, polyvinyl chloride, polyolefin compounds, rigid pressure pipe, solvent cements, thermoplastic elastomeric compounds, underground telecommunication cable duct, vent expansion joints, vent fittings, vent pipe, vinyl compounds, vitrified clay; plumbing supply fittings namely automatic compensating valves, bath and shower fittings, bidet fittings, components, supply stops; plumbing waste fittings namely components, elastomeric fittings, plumbing fixtures, valves

(6) Occupational health and safety products namely belts and saddles, descent control devices, eye protectors, explosive actuated tools, face protectors, fall arresting devices; ladders

(7) Adhesive-type labels namely electronic printing technologies, printing systems; building products and materials namely floors, roofs, vents; vehicle and road safety products namely helmets, photometric testing, helmets

(8) Direct fired agricultural heaters, brooder type agricultural heaters; burners namely gas fired; camping equipment namely lights, stoves, heaters, refrigerators, water heaters; carbon monoxide detectors namely commercial, safety shutoff and warning devices; comfort conditioning equipment namely air handling equipment, central type, dehumidifiers, heat pumps, humidifiers, evaporative coolers, unitary heat pumps; commercial dryers namely clothes dryers, crop dryers, spray booths, drying ovens; commercial gas cooking appliances, commercial electrical cooking appliances namely butane stoves, bain maries, baking and roasting ovens, coffee brewing equipment, deep fat fryers, food and dish warmers, foodservice equipment, hot plates or griddles, kettles, steam cookers, and steam generators, outdoor foodservice equipment, ranges and unit broilers, toasters, commercial heaters namely air, cargo carriers, construction use, duct furnaces, infrared, railway switch, trailer, unvented and vented, unit heater, water heaters, sand silo heater; domestic gas cooking appliances namely hot plates, outdoors, recreational vehicles, stoves, specialty appliances, door latch mechanisms; domestic heaters namely fireplaces, patios, radiant tube, space heaters, water heaters, gas-fired fireplaces, vented fireplaces; floor buffers; floor surfacing machines namely grinders, sanders, polishers; fuel burning equipment namely burners, commercial units, industrial units, stoves; gas accessory devices namely automatic combustion,

ventilation air control; heaters namely clothes dryers, cooking, liquid, portable, industrial, laboratory, pool; natural gas vehicle namely conversion kits, dispensing systems, dispensing systems, fueling appliances, fuel containers, fueling connection devices, manual valves; propane components namely fuel system components, miscellaneous; regulators namely compressed gas, gas appliance pressure, line pressure, low pressure, service; room heaters namely catalytic, unvented, vented; sealing compound; solid fuel burning equipment namely residential space heaters; steam cleaning machines; toilets; torches namely hand held; valves namely appliance connector, automatic, drop, electrical, flow, gas, lever-operated, manual, relief, shut off; water heaters namely electric storage tank,

(9) Actuators; anesthetic and medical gas equipment namely anesthetic machines, anesthetic ventilators, connecting assemblies, medical gas terminal units, oxygen analyzers, regulating and metering devices, resuscitators, vaporizers; appliance stands and drain pans; arc resistant equipment; asbestos-insulated wires; audible signal appliances; audio and video equipment and parts for electronic equipment, components, electromagnetic interference filters, kits, musical instruments, sound recording and producing equipment; automotive testing and repairing equipment; ballasts and ballasts ignitors; barbeque; building products and materials namely brick, cabinets, doors, foundations, gates, laboratories, laminates, panels, vanities, wall, windows; cable and cable fittings namely armoured, metal sheathed, feeder, neutral support, non-metallic sheathed, paper-insulated, thermoplastic and thermosetting; camping gas equipment; cart; cement; child resistant packaging; cleaning machines namely dishwashers, floors, wet scrubbing machine, steam cleaners; closure device namely locks, gates, rolling closure; controllers namely automated, flow; comfort conditioning equipment namely components, parts refrigerating machines and subassemblies; commercial amusement apparatus and components; commercial gas dryers namely industrial heat cleaning ovens; communication cords; concrete; conduit namely flexible metal, flexible nonmetallic, liquid-tight, rigid metal, reinforced thermosetting resin, rigid; connecting devices; connectors namely anchorage, electrical, gas, hose, pipes, swivel; cord reels; curtain; dip tubes; dishware; dispensing equipment namely for food, chemicals, liquids; draft equipment namely vents, hoods; drinking water equipment; electric generating plants; bonding and grounding of electrical equipment namely, ground clamps, ground lugs, grounding lugs; combustible fuel electrical equipment namely, switches; portable electrical equipment namely, fans, telephones; electrical parts for hygiene and cosmetic appliances, parts, heated, namely depilators and humidifiers; electronic components namely opto-isolators, resistors, sockets, thermistors; emergency lighting equipment; enclosures namely gaskets and seals; factory constructed buildings and structures namely kiosks, trailer running gear, trailers; hydromassage fans and blowers, exhaust fans and blowers; fire hydrant,

fire pump and components; fireplace; fittings namely flexible nonmetallic tubing, grounding and bonding, steel; dispensers; food dispensing equipment; freezer; fuel burning equipment namely, propane fuel burning equipment; furnaces namely combination fuel; fuel cell appliances; fuels handling equipment namely fuel tanks; gardening tools; gas accessory devices namely automatic ignition and components, automatic vent damper, combination control, combination quick disconnect /manually operated, digester gas controls, earthquake valves, earthquake automatic shutoff, gas pipe fittings, heat reclaiming, manual ignition, natural gas-operated diaphragm pumps, pilot ignition, quick disconnect, valve, vapor sensors; gas caps namely hose end valves; gas convenience outlets and enclosures; gas detectors; gas iron; gas switches; gas-tube signs; hand held tools namely band saws, circular saws, concrete vibrators, drain cleaners, drills, grinder, hammers, jointers, nibblers, polishers, planers, routers, sanders, screwdrivers, strapping, tappers, trimmers, wrenches, motor operated hand held tools; heaters namely battery warmers, engine, kilns, solar water, stationary baseboards, stationary type; hockey pucks; aquariums; breeding and rearing animals appliances; battery chargers; electric blankets; electric fences; electrical warming pad; electric rinsing sinks; electric steam cookers; foot warmers; heating mats; food waste disposers; fryers; garden ponds; electrical grills; ice-cream maker appliances; ice-maker appliances; lawnmowers; microwave ovens; projectors; range hoods; shredder appliances; spin extractor appliances; toasters; warming plate; water-bed heater; water suction cleaning; whirlpool; electric beds; electrical toothbrushes; foot massagers; hair clippers; hydromassage units; massage chairs; radiant heaters; infrared and ultraviolet lamp apparatus; information technology equipment namely disk storage drives, cartridge tape drives, word processors, business computers, expansion units, personal computers, portable personal computers, power supplies; insert fitting; insulating devices and materials namely cable joints, tubing and sleeving, underground cable; isolating, high voltage switches; lighting namely gas; lightning protection namely arresters; liquid dispensing equipment namely milk dispensing; low pass filter components; luminaires; marking systems namely adhesive attached marking, marking and labeling; medical electrical equipment namely blood pressure medical electrical equipment; defibrillator medical electrical equipment; electrocardiogram medical electrical equipment; electromechanical lifting devices medical electrical equipment; endoscopic medical electrical equipment; incubator medical electrical equipment; infant radiant warmer medical electrical equipment; lithotripsy medical electrical equipment; pacemaker medical electrical equipment; ultrasonic physiotherapy medical electrical equipment; ultrasonic diagnostic and monitoring equipment medical electrical equipment; motor protectors for temperature indicating and regulating equipment; molded cases for switches; multi-outlet assemblies, wiring systems and accessories namely powered table systems;

multiple receptacle extension boxes compressor systems; occupational health and safety products namely chain saws; pest control equipment; pilot gas filters; plumbing apparatus electric namely bathtubs, components and subsystems, pools, spas, toilets, tubs; plumbing fittings namely anti-siphon fill valves, closet and urinal spuds, flexible connectors, flush valves, flushometer and solenoid valves, supply line stops, temperature-actuated in-line mixing valves, thermal expansion relief valves, trap primers; plumbing fixtures namely backflow prevention devices, ceramic, concrete, enameled cast iron, glass, natural solid stone, porcelain enameled steel, septic and sewage holding tanks, water closets, stainless steel, tanks, thermoplastics, thermosetting plastics, water pressure reducing valves, water pumps; plumbing supply fittings namely faucets, mechanical stoppers and tubing, sink and shower strainer assemblies, subdrains for build-up shower pans; plumbing waste fittings namely traps and trap assemblies; pneumatic powered machines; polymeric raw materials namely wire and cable compounds; power generators namely cogeneration equipment, fuel cells, natural gas engine driven cogeneration, portable fuel cell, proton exchange membrane fuel cell modules, thermoelectric, metal supported solid oxide fuel cell modules; power supplies namely direct plug-in power supplies, cord connected power supplies, component power supplies, battery chargers, stand-alone power supplies; uninterruptible power supplies; architectural precast concrete; specialty precast concrete; structural precast concrete; pressure vessel; printed wiring boards; propane equipment namely appliances, heaters, lighters; pumps namely electrical, hand actuated hand pump, heat, water, liquids; raceways, wireways and busways and components, namely, auxiliary gutters and fittings, cabletroughs, cellular floor raceways and fittings for raceways, optical fiber and communication cable raceway systems, splitters, surface raceway fittings, surface raceways, underfloor raceway fittings, underfloor raceways; radio appliances namely surge traps; bathtubs, bathroom, boilers, electrical, equipment, gas, miscellaneous, toilets, showers, washroom, water pump; rectifiers; refrigeration equipment namely condensing units, drinking water coolers and fountains, recycling, refrigerating machines, refrigerant motor compressors; refuse processor; sensors; sheet liners and barriers materials; signal appliances, namely, kits, line isolation monitors; signs namely Christmas tree and other decorative lighting outfits; solder lug; tubular grates; sports safety equipment namely eye protectors, face protectors, helmets, visors; staples and straps for cable, armoured cable; surge suppressors; switchgear assemblies; telecommunications equipment, namely, remote power feeding telecommunications equipment; temperature indicating and regulating equipment, namely, baseboard heater limit controls, line voltage wall thermostats, thermal cut-offs; thermal blankets; thermal motor protectors; thermoplastic products and accessories; tool benches; torch boosters; traffic control equipment; transformer; vacuum pump; vapor abatement systems; vehicle and

road safety products; vehicle refueling appliances; waste sterilization namely ultraviolet, waste water treatment; wires namely coil-lead, control-circuit, flexible cord, fluoropolymer compound, mica-glass insulated, processed, thermoplastic, thermosetting, varnished cloth; wire connecting devices; wiring accessories namely pulling lubricants; wiring harnesses; zinc alloy fittings (10) Electrical business equipment namely, 15 bin sorters, 220V branch office controllers, 6085 professional computer systems, 9 inch printing accessories, access, accessory acoustic printer enclosures, accessory auto-duplex modules, accessory automatic document feeders, accessory cables, accessory controller cards, accessory document handlers, accessory electronic subsystems, accessory envelope feeders, accessory, floppy disk modules, accessory floppy/hard disk modules, accessory hard disk modules, accessory high capacity feeders, accessory imprinter heads, accessory input feeders, accessory keycounters for use with copiers, accessory kit graphics controllers, accessory labelling applicators, accessory memory cards, accessory memory processor boards, accessory microcomputer systems, accessory modems, accessory monitors, accessory offset catch trays, accessory paper handlers, accessory personal page printer adapters, accessory personal system display option and personal system memory options, accessory port expanders, accessory printers, accessory printing devices, accessory processor modules, accessory publishing systems, accessory sheet feed mechanisms, accessory sorters, accessory speech adapters, accessory stackers, accessory stamp heads, accessory stapler kits, accessory system power controls, accessory system stands, accessory tape, accessory telephone management modules, accessory terminal displays, accessory touch screens, accessory transceiver units, accessory two tray modules, accessory video displays, accessory work organizer kits, accessory-copy volume analyzer kits, accessory-high capacity feeders, accounting, accounting calculating and tabulating machines, accounting machines, acquisition subsystems, adapters, adaptors, alpha-numeric display terminals, alphanumeric sorters, application processors, area stations, asynchronous communication systems, asynchronous local distribution service units, attached processors, audio digitizers, audio responses, audio units, auto-feed hoppers, automatic data units, auxiliary power units, auxiliary printers, badge readers, bar code readers /decoders, bar code scanners, bar scanners, bar scanning scales, Barster, basic central systems, bin sorters, block multiplexors, bridge boxes, buffer boxes, buffers, bursters, cabinets, calculators, caller identification units teleconference terminals magnetically operated relays, card attachment units, card cage expansion kits, card data recorders, card proving, card punches, card reader options, card readers, card sorters, card units, cartridge disc drives, cash register accounting machines, cash register-displays, cash terminals, cassette tape drives, cassette terminal recorders, cassette terminals, CD ROM data storage, central control units, central processing

units, central processors, central processors and feature card files, change dispensers, channel attach, channel controllers, check encoders, check readers, check-out stands, clinical workstations (CWS), clocks, clothes washers, coax terminal multiplexers, color display monitors, color display stations, color displays, color monitors, color video monitors, color video terminals, colour press, comm. adapters comm. terminals, command /arithmetic, commercial teller terminals, communicating systems, communication bridges, communication connectors, communication control processors, communication controllers, communication gateway elements, communication servers, communication terminals, communications adapters, communications bridges, communications cable, communications expansion units, communications modems, communications processors, community antenna television cable, computer controls, computer elements, computer interconnect system, computer systems, configuration control register (CCR) signal translators, console printer keyboards, console TVs, consoles, consumer transaction machines, control adapters, control interface accessories, control modules, control unit accessories, control units, controller units, controllers, controls, conversational monitors, conversion accessories, conversion units, converters, conveyors, copier control devices, copier sorter accessories, copier systems, copier-printers, copiers, copiers with coin operated features, copy controllers, copy serializer accessories, copy volume analyzers, core memories, couplers, CPU systems, CPU units, credit authorization debit terminals, credit card imprinters, credit verifying units, data access units, data accessory cabinets, data acquisitions, data adapters, data cabinets, data capturing terminals, data cell drives, data channel units, data channels, data collection terminals, data collections, data communication cabinets, data communication processors, data communication terminals, data communications, data concentrators, data controllers, data couplers, data encryption devices, data entry stations, data entry terminals, data interface kits, data line scanners, data modems, data modules, data multiplexer, data processing systems, data punches, data racks, data recorders, data recorders, data retrieval units, data sets, data stations, data storage units, data stream converters, data systems, data tape stations, data terminals, dataway subsystems, dataway terminal multiplexers, decoders, deleaver attachments, deleavers, demand optical disks, demand terminals, desk console assemblies, desk station processors, desk top computers, device attachment control units, diagnostic tools, dial pulse operated recorders, dial units, dialers, digital disc drives, digital magnetic tape drives, digital sharing devices, digital telephone switching systems, digital telephones, digital voice announcers, digital voice messaging systems, digital voltage testers, direct plug-in transformer units, disc cartridge drives, disc drive controllers, disc drive units, disc drives, disc enclosures, disc file controller terminal units, disc file storages, disc file unit accessories, disc file units, disc files, disc pack drive

controllers, disc pack drive exchanges, disc pack electronic controllers, disc storage arrays, disc unit accessories, disc units, disk cartridge drives, disk drive cabinet assemblies, disk drive controls, disk drive subsystems, disk drive systems, disk file units, disk memory module, disk pack drive controllers, disk pack drives, disk pack testers, disk storage units, disk subsystems, disk units, diskette autoloaders, diskette subsystems, diskettes, display control units, display elements, display logic units, display monitors, display phones, display stations, display unit accessories, display units, displays, distributor, document handlers, document image scanners, document printers, document processors, document scanners, dot matrix serials, double insulated display monitors, double insulated power supplies, drives, dry ink cartridge/low ink level sensor kits, dual data stations, dual function terminals, duplicators, dust protection enclosures, electric typewriters, electroluminescent flat panel video monitors, electronic cabinets, electronic calculators, electronic cash registers, electronic correction systems, electronic desk top personal computers, electronic key telephone systems, electronic label readers, electronic line printers, electronic printers, electronic printing systems, electronic electric composers, electronic subsystems, electronic typewriters, electrostatic color copiers, electrostatic copiers, encoder printers, engineering drawing copiers, envelope addressors, environmental monitoring devices, equalizers, erasers, ethernet comm. servers, ethernet controllers, event recorder units, expansion cabinets, expansion controls, expansion modules, expansion units, facility access control units, facsimile machines, feature card kits, feed tractors, feeders, fiber optic channel extenders, field conversion kits, field installed accessories, field installed accessory portable disk modules, field installed kits, field installed units, field testers, field-installed accessories, file controls, financial data terminals, financial services terminals, financial terminals, finishers, fixed laser scanners, flexible disc drives, floppy disk units, floor stands, floppy/fixed disc drive kits, folder-stackers, formstackers, funds transfer terminals, fusing kit accessories, general purpose channel interface subsystems, graphic controllers, graphic systems, hard copy controls, high capacity auxiliary paper feeder kit accessories, high capacity stacker kits, high capacity stackers, image display processors, image output terminals, image scanners, imaging modules, imaging systems, impact printers, imprinters, independent transaction terminals, industrial control remote subsystems, ink jet color printers, input control units, input stations, input/output attachment enclosures, input/output cabinets, input/output expansions, input/output processors, input/output terminals, input/output units, inputs, instruction processor cooling units, instruction processors, instrument computers, instrument console units, intelligent network processors, intelligent terminal adapters, intercept switches, interchanges, interface path analysis tools, interfaces telephone systems, ion generators, ion printers, journal lister printers, journal

/validation printers, key counters, key telephone systems, key telephones, keyboard accessories, keyboard assemblies, keyboard controllers, keyboard displays, keyboard units, keyboards, keypad modules, key-to-cassette units, label applicators, label makers, labeling heads, laboratory peripheral systems, laminate trimmer, lamp transformer, laser beam printers, laser data storage devices, laser printers, laser scanning systems, level converters, line conditioners, line function units, line interrogation devices, line switching modules, link diagnostic units, link extenders, link protocol converters, listed accessory expander units KSU, lobby terminals, local distribution service units, loop fault finder drivers, loop fault finder terminators, mag card composers, mag card consoles, mag typewriters, mag. tape maintenance devices, magnetic card encoders, magnetic card readers, magnetic control units, magnetic drums, magnetic slot card readers, magnetic stripe card readers, magnetic stripe card readers/writers, magnetic stripe reader and encoders, magnetic tape, magnetic tape control units, magnetic tape drive units, magnetic tape drives, magnetic tape expansion cabinets, magnetic tape systems, magnetic tape transports, magnetic tape units, magtape controllers, maintenance consoles, maintenance diagnostic units, maintenance program load devices, magnetic tapes, manual entries, manual entry units, manual load diskettes, mass bus controllers, master control amplifier, master electronic controls, matrix printers, medium speed electronic printers, memories, memory back planes, memory units, message display, micro copiers, micro image readers, micro systems, microfiche duplicators, microfiche readers, microfilm modules, microfilm reader/printers, microfilmers, microprocessor development systems, microprocessor ROM programmers, microvaxes, migration data links, mini disk auxiliary units, minicomputer systems, minicomputers, mini-exchange communication, mixer preamplifier, mixers, mobile carts for data processing equipment, mobile computer systems modems, mod 24 terminals, model 4 production terminal consoles, models 1 2 terminal control units, modems monitors, modular instrument computers, modules, monitor terminals, monitors, monochrome display monitors, monochrome display stations, monochrome display units, monochrome image display stations, motion detectors, motor driven filing cabinets, motor winding heater, multicard units, multioutlet assemblies, multiple nests, multiplexors, multi-system channel communication units, network interface adaptors, network processors, non-impact printers, office furnishing panels prewired with electrical devices, offset catch trays, onyx telephone systems, open-type message display, operator consoles, optical character readers, optical character recognition units, optical data repeaters, optical disk storage drives, optical images, optical network, optical storage and retrieval units, output modules, output stations, packaged systems, packet interfaces, page printers, paging amplifiers, paper cutters, paper feeders, paper shredders, paper stackers, paper takeups, paper tape punches, paper tape units, paper tapes, paper tray

heater, paper tray heater kits, paper-tape readers, partitioners, partyline extenders, passbook and document printers, passbook printers, peripheral cabinets, peripheral control cabinets, peripherals, personal computers, photo copier, photo enlargers, photo plotters, photo printers, photocopier systems, plant communications controllers, plasma displays, plate setting machines, platen cover kits, plotters, point-of-sale terminals, portable computers, portable disk drives, portable terminal cradles, portable terminals, power adapters, power and collant dist. units, power controls, power converter units, power distribution units, power supplies, power supply accessories, power supply enclosure units, printed circuit assembly testers, printer controllers, printer terminals, printer/processors, printer/terminals, printers, printers printer ruggedized microsystems, printing financial services terminals, process controls, process op. panels, processor controllers, processor modules, processor storages, processor units, processors, programmable data terminals, programmable terminals, programmer/monitor, projection television receivers, protocol converters, punch switches, push-button stations, quarter folding machines, radio receivers, radios, raster image processors, reader-punches, readers, reader-sorters, recirculation document handlers, reduction processors, remote access maintenance units, remote attachment devices, remote audio response units, remote batch concentrators, remote concentrators, remote control modules, remote control panels, remote controls, remote copiers, remote job entry stations, remote keystation adapters, remote paralleling panels, remote power sequencing units, remote printer attachments, remote scanners, removable winchester systems, repeaters, reporting terminals, raster graphic subsystems, retail sales terminals, retail terminals, sampler readers, satellite interface, satellite receiver /descramblers, scan masters I, scanner, scanner accessories, scanner control units, scanner/scales, scientific information processors, security interface units, selectors, selectric testers, semi automatic document handlers, serial printers, servers, sharded disk cabinets, sheet feeders, signal converters, signal distribution module, single function terminal and concentrators, single function terminal expanded, single pocket proof machines, solid-state disks, sorting equipment, stacker accessories, stand alone line driver expanded, stand-alone power supplies, station control storages, statistical multiplexers, stereo decoders, storage units, storages, streaming tape drive cabinets, subsystem availability units, subsystem control units, subsystem power controls, supermarket terminals, switching management systems, switching units, switchings, system clock units, system consoles, system control consoles, system control units, system controllers, system testers, table top readers, tape automated loaders, tape conditioners, tape connectors, tape control units, tape disc cabinets, tape disc subsystems, tape drive cabinets, tape drive units, tape drives, tape microde interfaces, tape storage units, tape subsystems, tape systems, tape transmissions, tape transports, tape units, telecopiers, telephone line

controllers, telephone switchboard accessories, telephone systems, telephones power systems, teleprocessing concept trainers, teletext decoders, television monitors, television receivers, teller extension, terminal adaptors, terminal attachments, terminal concentrators, terminal concentrators, terminal connectors, terminal control units, terminal controls, terminal display units, terminal entry stations, terminal interfaces, terminal multiplexers, terminal printers, terminal servers, terminal sets, terminal systems, terminals, testers, text editing terminals, ticket converters, ticket encoders, time and attendance terminals, time base corrector/transcoders, time-delay cash boxes, timers, tone generator, tone-to-pulse converters, transaction accounting systems, transaction machines, transceivers transformer accessory for carts, transcribers, transfer switches, translators, transmission controls, tray modules, trimmer, tuner-tape player, TV-FM amplifiers, typewriters I/O, unibus expander cabinets, universal communication front ends, universal product code readers, universal transcoders, VCR adaptors, vector stroke systems, vending machines SME John Jakob, video cassette players, video cassette recorders, video data terminals, video decoders, video display monitors, video display units, video displays, video encoders, video imaging systems, video optical network interfaces cable communication equipment, video port controllers, video processors, video system boxes, video terminals, video text terminals, viewers, VIP peripheral cabinets, voice branders, voice information processors, wedge box printer interfaces, wiring concentrators, word processing units, work station scanners, zip code separators; wires namely, aboveground reinforced thermosetting resin conduit, aboveground reinforced thermosetting resin conduit fittings, accessories whose principal function is for support of boxes, airport series lighting cables, appliance plugs for heater cord sets, arc-welding cable, armoured cables, associated fittings for completing wireway systems, attachment plugs receptacles, auxiliary gutters, belowground reinforced thermosetting resin conduit, belowground reinforced thermosetting resin conduit fittings, branch-circuit busway associated fittings, branch-circuit busways, cable and cord connectors couplers and flanged equipment power inlets and flanged equipment power outlets, cable connectors of the pin and sleeve type, cellular concrete floor raceway fittings, cellular concrete floor raceways, cellular metal floor raceway fittings, cellular metal floor raceways, closure plugs, communication cable raceway systems, conductive optical fiber cable, connectors that are intended to enclose the ends of gas tube electrodes and to provide a connection to the secondary voltage supply, cord and cable reels, cord reels, cord-connected multiple receptacle extension boxes, dlo cable single conductor used for portable and general applications, electrical non-metallic tubing, electrical non-metallic tubing mechanically-attached fittings, electrical quick-connect terminal connectors, electrical quick-connect terminal tabs, electrical wires, electrode connectors for gas tubes, electrode fittings for gas tubes, electrode fittings for

mounting gas tubes, electrode receptacles for gas tubes, electrode receptacles for mounting gas tubes, extension rings, extra-low-voltage control cable, extra-low-voltage control circuit cable, fire alarm cable, flexible cable for use with cranes, flexible cable for use with hoists, general use and hospital grade moulded-on attachment plugs, general use and hospital grade moulded-on cord connectors, handset cords, industrial locking type special use attachment plugs, industrial locking type special use connectors, industrial locking type special use receptacles, interconnecting cable assemblies, interconnecting cables, liquid-tight flexible non-metallic conduit, locking type equipment power connectors, locking type equipment power inlets, locking type equipment power outlets and connectors, locking type plugs, locking type receptacles, low-energy control cable, manufactured wiring products, marine application flush-device boxes, marine application covers, marine application extension rings, marine application metallic outlet boxes, marine application special purpose boxes, marine shipboard cable, medium voltage cable, metal cable tray systems, metal sheathed cables, metal surface raceway systems, metal-clad cable, metal-clad cable connectors, metallic bar hangers, metallic bar-hanger assemblies, metallic box extenders, metallic concrete boxes, metallic conduit bodies, metallic covers, metallic extension rings, metallic floor boxes, metallic flush-device boxes, metallic outlet boxes, mine power feeder cables, mineral-insulated cable, mineral-insulated cables with copper enclosed in a stainless steel sheath, mineral-insulated cables with copper enclosed in a copper sheath, mineral-insulated cables with nickel conductors enclosed in a stainless steel sheath, mineral-insulated cables with nickel conductors enclosed in a copper sheath, mineral-insulated cables with nickel-/nickel-alloy-clad copper enclosed in a stainless steel sheath, mineral-insulated cables with nickel-/nickel-alloy-clad copper enclosed in a copper sheath, mineral-insulated cables with steel-clad copper enclosed in a stainless steel sheath, mineral-insulated cables with steel-clad copper enclosed in a copper sheath, multi-conductor constructions without metal sheath or armour suitable for use in cable trays and other applications, multiconductor PPC cables for general applications, multi-conductor type TECK 90 armoured cable, multiple-conductor fire alarm cables, multiple-conductor signal cables, multiple-gang boxes, neutral-supported cables, non-conductive optical fiber cable, non-metallic box extenders, non-metallic cable tray systems, non-metallic conduit associated fittings, non-metallic conduit bends, non-metallic conduit concrete floor boxes, non-metallic conduit elbows bends, non-metallic device boxes, non-metallic mechanical protection tubing, non-metallic outlet boxes, non-metallic pull boxes, non-metallic sheathed cable, non-metallic surface raceway fittings, non-metallic surface raceway systems, non-metallic surface raceways, optical fiber cables, outlet box covers, pin and sleeve type plugs receptacles power inlets and connectors, plugs intended for use in electronic and electrical applications, plugs receptacles of the pin and sleeve type, portable power cables, power and control tray

cable, power connectors intended for use in electronic and electrical applications, power inlets intended for use in electronic and electrical applications, power limited circuit cable, power outlets intended for use in electronic and electrical applications, power supply cords, PVC insulating tape, receptacles intended for use in electronic and electrical applications, receptacles with attachment plugs, receptacles with attachment plugs interlocked with circuit breakers, receptacles with attachment plugs interlocked with switches, rigid PVC (unplasticized) conduit bends, rigid PVC (unplasticized) conduit couplings, rigid PVC (unplasticized) conduit elbows, rigid types DB2/ES2 pvc conduit, rigid types EB1 PVC conduit, service entrance cable and fittings, service-entrance feeder busway, service-entrance feeder busway associated fittings, signal cable, similar wiring devices intended for use in electronic and electrical applications, single conductor constructions without metal sheath or armour suitable for use in cable trays and other applications, single- conductor fire alarm cables, single conductor PPC cables for general applications, single- conductor type T 90 armoured cable, single- or multiple-conductor, jacketed or unjacketed, integral or non-integral cables, and single or multiple coaxial cables for telephone and other communication circuits such as voice data and audio for on-premise customer systems, single-conductor portable power cable, single-conductor signal cables, special use attachment plugs, special use connectors, special use receptacles, splicing cable connectors, splitters, thermoplastic-insulated cables, thermoplastic-insulated wires, thermoset and PUR multiconductor round cables for mining and general applications, thermoset three-conductor round cables with a central bonding (grounding) conductor for underground coal mining applications, thermoset two- and three-conductor flat cables for mining and general applications, thermoset-insulated cables, thermoset-insulated wires, tray cables, tubular support members and associated fittings for domestic and commercial service masts, type FCC under-carpet wiring system, underfloor raceway fittings, underfloor raceways and fittings, underground secondary cables, underground service-entrance cables, variable frequency drive cable three conductor round or mining and general applications, wire connectors, wires of common metal, wireways auxiliary gutters and associated fittings, wireways for insulated wires and cables, wiring terminals and supporting blocks for aluminum conductors, wiring terminals and supporting blocks for copper and aluminum conductors, wiring terminals and supporting blocks for copper conductors, appliance wiring material products namely, single- or multiple-conductor round appliance wiring material products for internal wiring of equipment (single- or multiple-conductor constructions with or without a covering or jacket), single- or multiple-conductor flat appliance wiring material products for internal wiring of equipment (single- or multiple-conductor constructions with or without a covering or jacket), single- or multiple-conductor coiled appliance wiring material products for internal wiring of equipment (single- or multiple-conductor constructions

with or without a covering or jacket), connectors for use with aluminum conductors, connectors for use with copper conductors, pressure wire connectors intended to hold one or more conductor, connectors intended for use in appliances and equipment, soldering connectors, splicing wire connectors, neutral bars, uninsulated connectors, ampere-rated connectors not intended for general use, insulation piercing connectors, pull boxes, cutout boxes and junction boxes namely, non-metallic cutout boxes, metal cutout boxes, non-metallic junction boxes, metal junction boxes, metal pull boxes, non-metallic pull boxes, rigid PVC boxes and fittings namely, junction boxes, conduit boxes, surface mounted device boxes, device box covers, blank box covers, expansion joints, junction box terminal adapters, female adapters, reducers, caps, bell ends, extruded insulating tubing namely, heat-shrinkable tubing, crosslinked tubing, coated electrical sleeving namely, Grade A acrylic-polymer-coated electrical sleeving, Grade A silicone-polymer-coated electrical sleeving, Grade A vinyl-polymer-coated electrical sleeving, Grade B acrylic-polymer-coated electrical sleeving, Grade B silicone-polymer-coated electrical sleeving, Grade B vinyl-polymer-coated electrical sleeving, cable ties for electrical installations namely, metallic cable ties and their associated fixing devices, non-metallic cable ties and their associated fixing devices, composite cable ties and their associated fixing devices, sealed wire connector systems namely, insulating caps, insulating covers, insulating resins, insulating tubing, insulating tapes, insulated multi-pole splicing wire connectors namely, multi-pole non-mating splicing wire connectors, multi-pole mating splicing wire connectors, electrical resistance heating cables and device sets namely, heating cables cable sets and, surface heating device sets, electrical wires, electrical cables, flexible cords and cables namely, flexible cords elevator cables, hoistway cables, service cords, elevator cables, heater cords, range cords, dryer cords, cords for decorative lighting, tinsel cords, lamp cords, special use cords, equipment wires namely, lead wires, insulated conductors intended for internal wiring of electrical equipment for leads of transformers motors, insulated conductors intended for internal wiring of electrical equipment for luminous-tube signs, insulated conductors intended for internal wiring of electrical equipment for ignition systems, cords for communication systems namely, cord sets for communication systems, single-conductor cord sets, single-conductor cords, paired-conductor cords, paired-conductor cord sets, multi-conductor cords, multi-conductor cord sets, control and instrumentation cables namely, multiple-conductor control cables, instrumentation cables, thermocouple cables, thermocouple extension cables, multiple-conductor thermoplastic or thermoset-insulated assemblies, shielded or unshielded, twisted or cabled, paired or grouped into units, jacketed or unjacketed, sheathed or unsheathed, armoured or unarmoured, and any combinations thereof cables, general use receptacles attachment plugs namely, wiring devices of the general purpose nonlocking and locking types, general use attachment plugs, hospital-

grade attachment plugs, adapters without male or female screwshell, general use receptacles including those intended for use with aluminum wire and those of the self-contained type, hospital-grade receptacles including those intended for use with aluminum wire and those of the self-contained type, general use cord connectors, hospital-grade cord connectors, current taps and similar devices such as flanged equipment power inlets and outlets, devices for use with copper conductor non-metallic sheathed cables for mounting without a separate outlet box, self-contained receptacles intended for flush mounting, surface-mounted receptacles, cover plates for flush-mounted wiring devices namely, non-metallic cover plates and associated gaskets for flush-mounted wiring devices, metallic cover plates and associated gaskets for flush-mounted wiring devices, outlet box hoods, cover plates for flush-mounted wiring devices intended for use in marine applications, metal-enclosed high-voltage busways namely, outdoor metal-enclosed busways, indoor metal-enclosed busways, straight bus sections, elbows, tees, wall flanges, forced-cooled busways, nonforced-cooled busways, isolating links and, expansion joints, constructions with rigid bus conductors, constructions with cable type conductors; agricultural equipment namely, agricultural cultivators, agricultural equipment for seeding, agricultural irrigation equipment, agricultural land fertilizing equipment, agricultural plows, agricultural tractors, animal clippers, animal shearers, battery-operated electric fence energizers suitable for connection to the mains, brooders, bucket milking machines, direct-to-can milking machines, electric brooders for use inside buildings on commercial hatcheries, electric brooders for use inside buildings on farms, electric fence controllers, electric fence energizers, electric fence energizers operated by non-rechargeable batteries either incorporated or separate, electrical heating appliances for breeding and rearing animals, incubators, independent air and milk transport milking machines, indoor types of electric fence controllers that utilize either peak-discharge or timed-sinusoidal circuits, livestock feed boilers, mains-operated energizers, milking machines, milking pipeline machines, outdoor types of electric fence controllers that utilize either peak-discharge or timed-sinusoidal circuits, portable and stationary domestic and commercial electric incubators, recorder milking machines; circuit breakers and accessories namely, auxiliary and trip alarm switches, auxiliary switches, circuit-breaker enclosures, cylindrical locks, enclosures for circuit breakers, fuse-holders for miniature cartridge fuse-links, instantaneous-trip circuit breakers/circuit interrupters, interphase barriers and hasp locks, isolators, lightning arresters, line or load shrouds, mechanical interlocks, miniature fuses, molded-case circuit breakers, molded-case circuit breakers for marine use, molded-case circuit breakers for naval use, molded-case circuit breakers for software in programmable components, molded-case circuit breakers for uninterruptible power supply use, rotary handles, shunt trip devices, solenoid operators, under voltage trip devices, ground-fault circuit-interrupters, single-phase ground-fault circuit-interrupters, capacitors

for power factor correction, indoor and outdoor shunt power capacitors and assemblies for power factor capacitors with associated interconnections and supporting structures for power factor improvement and other applications, open or enclosed shunt power capacitors and assemblies of shunt power capacitors with associated interconnections and supporting structures for power factor improvement and other applications; comfort conditioning equipment accessories namely, air conditioner or furnace controllers, data collection and temperature monitoring systems, hermetic refrigerant motor-compressors, temperature sensors, thermostatic controls, thermostats, line voltage room thermostats, pressure limit switches, humidity controls, electrically operated valves, damper actuator, valve actuator, safety controls involving functional safety, including software evaluation, air conditioning and ventilation equipment namely, air conditioning equipment and accessories, air ducts and connectors, air filter units, central cooling air conditioners, dehumidifiers, electrostatic air cleaners, exhaust hoods without dampers, fire damper operators, fire dampers, heaters, heating appliances and heating equipment namely, air heaters, baseboard heaters and accessories, bingo card erase cabinets, ceiling heaters, central furnaces, combustible liquid-level gauges, ducted heat recovery ventilators, engine heaters, fan-coil units for heating, Single operating devices (SOD), gas ignition control, floor heaters, gas burners, gas-fired boiler assemblies, gas-oil burners, gas-oil-fired boiler assemblies, generators, heated display cabinet, heated holding cabinet, heaters, heating cables, heating limit controls, industrial and laboratory heaters, infrared portable panels, mobile home pipe heating cable, mobile infrared ovens, modular food tables, oil burners, oil fired central furnaces, oil level sensor, oil-fired boiler assemblies, pipe heating cables, plastic pipe heating units, portable fireplace, pressure steam, proofing cabinets, radiant heaters, radiant heating cables, radiant heating panels, solid fuel-fired boiler assemblies, steam bath generators, under-concrete heaters, wallpaper strippers, warming trays, water distillers, water meters, heaters, heating appliances and heating equipment namely, air heaters, baseboard, waterbed heaters, heaters and accessories, accumulators, condensers, evaporators, dryers filters, heat exchangers, oil separators, liquid receivers, mufflers liquid indicators, vibration eliminators, strainers, fusible plugs, rupture members, heating and cooling equipment namely, heat pumps for heating and cooling with or without factory- or field-installed electric resistance heaters or hot water or steam heating coils, air conditioners for cooling with or without factory- or field-installed electric resistance heaters or hot water or steam heating coils, cooling portion and associated components of combination heating and cooling equipment employing gas-, oil- ,or gas-oil-fired heating means, liquid chillers and compressor-evaporator or liquid chiller assemblies intended for use with remote condensers, condensing units intended for connection to a remote non-specified evaporator and compressor units intended for connection

to a remote non-specified evaporator and condenser, add-on heat pumps for comfort heating or heating and cooling, heat pump, water heaters, refrigerant desuperheaters and packaged heat pump water heaters consisting of a heat pump water heater and an associated storage tank, fan units and fan coil units for comfort heating and/or comfort cooling, room fan heater units, central heating furnaces and similar fixed electric space heating for comfort heating, fan unit (a motor-operated fan or blower and is intended to be connected to a duct system that supplies conditioned air for environmental heating and/or cooling), fan coil (a motor-operated fan or blower together with a cooling coil or a heating coil or both. The fan or blower is intended to recirculate air and may introduce air from outside of the heated or cooled space), electrostatic air cleaners namely, electrostatic air cleaners intended to remove dust and dirt from the air and intended for general indoor residential and commercial use; air ionizer type air cleaners; other similar ionizing equipment; insect killers or insect control equipment; control equipment namely: automatic electrical controls for household and similar use, burner ignition systems and components using oil, natural gas, manufactured gas, mixed gas, liquefied petroleum gas or liquefied petroleum gas-air mixtures, electrical control equipment for refrigeration, electrical control equipment for air-conditioning, electrical control equipment for cooling, electrical control equipment for heating, electrical control equipment for lighting, process variable detectors for temperature, pressure, pH level, voltage, flow rate, humidity level, volume size, capacitance, light levels and electronic motion sensors, process variable recorders for temperature, pressure, pH level, voltage, flow rate, humidity level, volume size, capacitance, light levels and electronic motion sensors, process variable sensors for temperature, pressure, pH level, voltage, flow rate, humidity level, volume size, capacitance, light levels and electronic motion sensors, receivers control units used in the sensing recording and transmission of signals, these equipment may be stand alone or components for use with other electrical equipment controls for electric gas oil solid fuel and solar thermal energy source appliance or a combination thereof mechanical or electrically operated controls starting relays ntc control ptc thermistors controls, transceivers control units used in the sensing recording and transmission of signals, transmitters control units used in the sensing recording and transmission of signals; electrical controls for electrical household appliances namely, automatic electrical controls mechanically or electrically operated responsive to or controlling such characteristics as temperature, pressure, passage of time, humidity, light, electrostatic effects, flow or liquid level, current voltage, or acceleration, starting relays, Signal Equipment, Starting Relays, manual controls; data processing equipment namely, computers, 35 mm accessories, access concentrators, accessory finishers, accessory keyboards, accessory kit for computers, accessory network adapters, accessory printer options, acoustic couplers, acquisition systems, ADSL modems, analog data modules, analog terminal adapters, analogue

modems, analogue to digital video capture cards, antenna, antenna module, arpanet interface units, auditron accessories, badge printers, badge readers, bar code readers, battery chargers, book keeping machines, cable modems, caller identification, card puncher, card readers and writers for cards having chips or magnetic strips, central processing units, central processor modules, channel interfaces, channel servers, CI switches, communication buss, computer audio cards, computer forms feeders CFP kits, computer output processing systems, computer power centers, computer power units, computer system main operator's consoles, computer system mainframe units, computer system power distribution units, computer system remote operator's consoles, computer systems, computer terminals, cordless telephone, CPUs, CRT display monitors, CRT stands, data collection units, data port expanders, dc to ac inverters, AC to DC converters, demodulators, desk consoles, digital camera, digital modems, digital organizers, digital signal switches, digital telephone switcher, digital video camera, digital voice recorders, disk driver controllers, disk enclosures, disk storage systems, dot matrix printers, double insulated computer equipment, drum heater, dual line switches, electromagnetic interference filters, electronic digitizers, electronic memory systems, electronic message systems, encoders, encryptors, environment recording devices, ethernet bridges, ethernet floor stands, ethernet systems and components, even recorders, external memory devices, field installed accessories, fingerprint scanners, floor terminals, floppy disc modules, floppy disk drives, floppy /hard disk modules, graph plotters, graphic processors, graphics digitizers, graphics modules, hand writing capturing devices, hand-held scanners, hard disk modules, hard drives, independent I/O units, information distributors, information processors, ink cartridges, ink jet printers, input/output modules, interactive terminals, interfaces, key counter kits, key counters, key counters for use with copiers, label printers, laser printer engines, laser printers, LED power module, LED printers, light pens, line drivers, line printers, local area networks, logic power controllers, logic units, loop to ground start converters, magnetic tape drives, main frame computers, mass storage units, media input adapters, memory cards, memory control modules, micro computer systems, micro computers, micro processors, microphones, microprint drives, microservers, microsystems, microvox, mode analyzers, modem controls, modem expanders, modems, modular controllers, modular data center, modulators, mounting cabinets, mouse, multidisk drives, multiplexers, multiplexor units, multiprocessors, multistation access units, network interfaces, network modules, optical communication devices, optical demultiplexers, optical digital couplers, optical multiplexers, optical reader, optical writers, outdoor enclosures, packet network interfaces, PBX, peripheral multiplexors, peripheral switches, personal computers, personal image processors, phone ringer generator, plotter, portable disk drives, portable viewers, power adapters, power converter units, power

distribution units, power logic boxes, power supplies, printed wiring boards, printers, printing kiosk, private data exchanges, processor modules, processors, programmable industrial control systems utilizing a programmable memory for internal storage of user oriented instructions, protocol retail terminals, rack mounts, remote cluster controllers, remote consoles, repeaters, retrofit kits tape converters, router, satellite, satellite boxes, satellite receiver/ descrambler, scanner scales, scanners, self service terminals, semiconductor memory systems, servers, shared memory controls, site data acquisition systems, sliding rails for cabinets, sorting machines, speech converters, starlan hubs, store controllers, switchboards, synchronous communication data boxes, telephone base stations, telephone couplers, telephone management systems and accessories, telephone modules, telephone recorders, telephone switch, telescopes, teletype terminals, terminal cluster controllers, terminal controllers, terminal equipment units, terminal units, test sets, ticket issuing machines, token ring adapters, tone to pulse recorder, unibus expansion cabinets, USB interfaces, video display terminals, video monitors, videotex decoders, web cameras, word processors, work stations, writing devices, zip code scanners; dental equipment namely, air abrasion, air drying systems, compressors, curing light accessories, curing lights, cuspidors, dental drills, dental stools, digital radiography, high speed hand pieces, lights, ultrasonic cleaners, ultrasonic scalers, vacuum pumps, washing and disinfection devices, x-ray equipment; supply fittings namely, air admittance valves, automatic compensating valves for individual showers and tub/shower combinations, automatic compensating valves for ganged showers and tub/shower combinations, individual thermostatic pressure balancing and combination thermostatic/pressure balancing valves for individual fixtures backflow protection devices and systems in plumbing fittings, bath and shower fitting, bath shower diverter valve with integral backflow protection, valves (in-line pressure balancing), valves (pressure balancing), valves (pressure regulating), water temperature limiting devices, commercial faucet with an integral emergency eye wash unit, emergency eyewash and shower equipment, emergency shut off devices, temperature actuated mixing valves for plumbed emergency equipment, diverter valve (ABS), bidet fitting, drinking fountain bubbler, electric lavatory and electric faucet, faucets, hand held shower, kitchen faucet, kitchen faucet with pull out hose, laundry faucet, lawn and sediment faucets, hydrants (frostproof), valves (PVC & CPVC wall hydrants (frostproof) with alternate end connections, low flow laundry faucet, metering faucet, plumbing fixture fittings compliant to NSF 61 section 9, plumbing fixture waste fitting, pot filling faucet, pre rinse spray valve, self closing faucet, shower diverter valve, shower fitting, showerhead, supply fitting, supply line stops, thermal expansion relief valves (TER), valves (in-line & end point application), water efficiency products namely, EPA watersense high efficiency flushing urinals/urinal flushing

devices, EPA watersense high efficiency lavatory faucet aerators, EPA watersense high efficiency lavatory faucets, EPA watersense high efficiency toilets, watersense high efficiency showerheads, fixtures namely, adjustable position sinks, adjustable elevating tilting and pivoting lavatory, sink and shampoo bowl carrier systems, bathtub / shower enclosures and shower panels with fittings, bathtub liners, bathtub with pressure sealed doors, bathtub /shower pan liners, bathtub/showers (plastic bathtubs (acrylic & fiberglass), bathtubs (cultured marble), bathtubs (plastic), bathtubs with over-the-rim overflow drain receptor, bathtubs with pressure sealed door and drainage tank, bathtubs with pressure sealed doors, bath waste and overflow assemblies with tub filler spout, bidet, ceramic plumbing fixtures, copper or aluminum alloy sinks & lavatories, doctor scrub sinks, drinking water fountains and drinking water coolers, enamelled cast iron and enamelled steel plumbing fixtures, glass lavatory, laundry basin, laundry trays (polyester), lavatories, lavatories & sinks (vitreous china), lavatories (plastic), lavatory (ABS/acrylic), lavatories (stainless steel), macerating toilet systems and related components, metallic bathtubs and whirlpool bathtubs, pedestal lavatory, plastic water closet tank, plumbing fixture (cast iron), plumbing fixture (vitreous china), plumbing fixture fittings, plumbing fixtures (enamelled cast iron), plumbing fixtures (lavatories), plumbing fixtures (non-vitreous china), plumbing fixtures (porcelain enamelled steel), plumbing fixtures (stainless steel), pre-fabricated tileable shower receptors, shampoo sinks, shower (plastic), shower door, shower pan liner, shower panel, shower pan liners (CPE), shower pan liners (PVC), shower panel assembly, shower walls (plastic), sinks (plastic), sinks (stainless steel), six-litre water closet equipped with dual flushing device, stainless steel industrial/commercial sinks, stainless steel waterless urinal, terrazzo marble concrete or granite plumbing fixtures, tub/shower enclosures with factory-installed fittings, tub/shower enclosures with pre-installed fittings, door and threshold assembly, urinals (waterless/vitreous china), vitreous china water closet with overflow, wash fountains and lavatory systems, water closet personal hygiene devices, water closet tank (wall hung w/carrier), water closets with dual flush feature, water closets with integral rinse station, water dispenser, waterless urinals (plastic), fabricated stainless steel water closets, lavatories and urinals, fixture components namely, dual flush device, early closure flapper (retrofit), grab bar anchor, grab bars, fill valve & flush valve combination, fill valves (anti-siphon), fill valves or flushometer valve, flush valves flushometer tank, flushometer valves (urinal or wc), flushometer valves (urinal), pressurized flushing devices, fixtures and fittings namely, cable clamps cable, cable fittings, cable tie mounting blocks, cable ties, conduit bodies, conduit bodies for rigid polyvinyl chloride (PVC) conduit, conduit bushings, conduit clips, conduit locknuts, conduit tubing, electrically operated water valves, entrance elbows, fittings for tray cable, fittings for aluminum-sheathed cable, fittings for armoured cable, fittings for electrical metallic tubing, fittings for flexible cord, fittings for flexible metal

conduit, fittings for flexible metallic tubing, fittings for flexible non-metallic tubing, fittings for insulating bushings grips reducing nipples, fittings for insulating bushings grips reducing washers, fittings for intermediate metal conduit, fittings for liquid-tight flexible conduit, fittings for metal-clad cable, fittings for mineral-insulated cable, fittings for non-metallic-sheathed cable, fittings for rigid metal conduit, fittings for service-entrance cable and, fittings for service-entrance heads, fixtures and lamps and typewriter attachments, hangers staples straps, hardware for the support of cable, hardware for the support of conduit tubing, metal stud bushings, metallic and non-metallic devices used for positioning and bundling and securing, non-raceway ducts, positioning devices, standoffs for non-metallic-sheathed cable, standoffs for non-metallic-sheathed protector plates, submersible fittings, supporting cable wire conduit or tubing of a wiring system in electrical installations; gas accessory devices namely, electronic controllers for flow monitoring sensors and for flow alarm sensors, electronic temperature controller for gas analyzing devices, flame safety control units, flow alarm sensors, flow meters, flow monitoring sensors, fuel valves, high limit temperature controls, pressure sensors, temperature sensors; household and commercial appliances namely, aerators, air-cleaning appliances, air-cooled window or console or built-in-wall type room air conditioners, alarm clocks, an-type air-to-air heat exchangers, appliances for heating liquids, appliances for skin exposure to ultraviolet and infrared radiation, appliances provided with a worm conveyor such as mincers, noodle attachments, and berry juice extractors, aquarium heaters, aquarium pumps, attic ventilating-type fans and ventilators, automatic food dispensers, baby-food grinders and choppers, baby-food warmers/servers, bake /roast ovens, barbecue lighters, barbecues, barbecues for indoor use, battery chargers, bean slicers, beaters, berry-juice extractors, beverage cooler-dispensers refrigerators, beverage cooler-freezers, beverage cooler-refrigerators, beverage coolers, blenders, blenders for food, blenders for liquids, bottle warmers, breadmakers, broilers, built-in freezers, built-in refrigerators, bun warmers, can openers, ceiling insert ventilating-type fans and ventilators, centrally-sited vacuum cleaners, centrifugal atomizing humidifiers, centrifugal juicers, centrifugal juicers for fruit and vegetables, chafing dishes, cheese graters, churns, citrus fruit juice squeezers, clocks, clocks incorporating driving means other than motors, clothes dryers, clothes dryers and towel rails, clothes washing machines, combination kettle/hydraulic mixer, combination steam generators and steam cookers and/or kettles, commercial boiling pans, commercial clothes iron, commercial dishwashers, commercial electric bains-marie, commercial electric boiling pans, commercial electric cooking ranges ovens hobs and hob elements, commercial electric deep fat fryers, commercial electric dishwashing machines, commercial electric forced convection ovens steam cookers and steam-convection ovens, commercial electric griddles and griddle grills, commercial electric grillers, commercial electric hot cupboards, commercial electric

kitchen machines, commercial electric multi-purpose cooking pans, commercial electric rinsing sinks, commercial electric toasters, commercial freestanding counter-insert dishwashers, commercial freestanding counter-insert glass washers, commercial freestanding counter-insert utensil-washers, commercial freestanding under-counter dishwashers, commercial freestanding under-counter glass washers, commercial freestanding under-counter utensil-washers, commercial vegetable slicers/shredders, compressor units, condensing units, contact grills and griddles, controls for heating-cooling appliances and accessories transfer bins, convection ovens, convector heaters, convention ovens, conveyor ovens, cookers, cookers steam, cooking pans, cooktops, coolers for raw milk intended for farm use permanently connected of the bulk direct expansion ice bank type having either a self-contained or remote condensing unit, cooling and ventilating equipment, cord-connected appliances for household and commercial use, corn poppers, cream whippers, crepe-makers, deep fat fryers frying pans, deep-fat fryers, dehumidifiers, desk fans, dishwashers, domestic electric ironing machines, door and frame assemblies used as part of a refrigerated room or cabinet, dough molders, doughnut-makers, effects projectors, egg beaters, egg boilers, egg-cookers, electric built-in household cooking ranges, electric clothes dryers, electric clothes dryers for drying textiles on racks located in a warm air flow and to electric towel rails for household and similar purposes, electric clothes washing machines and extractors, electric clothes washing machines and extractors provided with coin- ticket- or card-operated mechanisms wringer washers tumbler agitator and spinner machines combination washer-dryers and extractors of the centrifugal type, electric dry irons, electric fans, electric hot pots, electric household cooking ranges, electric household cooking ranges in combination with gas coal wood or oil-fired heaters, electric irons, electric kettles, electric ranges, electric washing machines for household and similar purposes intended for washing clothes and textiles, electrical air-conditioners, electrical appliances for use with aquariums and garden ponds, electrical dehumidifiers, electrical heat pumps, electrical heat pumps air-conditioners and dehumidifiers, electrically heated blankets pads, electronically commutated (brushless) dc component fans, embossers, equipment designed to be field-installed as part of a refrigeration system such as remote display cases and unit coolers, equipment designed to produce some degree of freezing of food or beverage mixtures and to dispense them at will from the equipment at the time of sale, evaporative-media humidifiers, exclusive of any other use steam generators not intended for household use, fan heaters, fans and ventilators, feeding-bottle heaters, file/pie/chicken stations, film viewers, film-strip projectors, fixed in a cabinet clothes racks, flexible heating appliances, floor buffers, floor treatment machines and wet scrubbing machines, floor waxers, food cooking and warming appliances, food dehydrators, food mixers, food processors, food warmers, food waste disposers, forced

convection ovens, freestanding freezers, free-standing in a cabinet clothes racks, freestanding refrigerators, freezers, freezers for use in recreational vehicles, fry kettles, frypans, gas and electric ranges, glue guns, glue pots with a water jacket, grain grinders, graters, graters and shredding appliances for vegetables and fruits, griddles, grills, grills toasters and similar portable cooking appliances, grinders, hamburger-cookers, hand or hair dryers, hassock fans, heaters for use in greenhouses, hedge trimmers, high pressure cleaners and steam cleaners, hot carts, hot dog cookers, hot melt adhesive guns, hot pots, hot-dog-cookers, hotplates, household dishwashers, household electric ranges, household freezer accessories, household hood or canopy ventilating-type fans and ventilators, household refrigerator accessories, humidifiers, humus (or chemical) electric toilets, ice cream makers, ice crushers, ice dispensers, ice makers, ice making machines that manufacture and harvest ice in cube flake or other readily usable form and that may or may not incorporate ice storage means, ice-cream appliances and ice-makers, ice-cream appliances including bucket type and those for use in refrigerators, ice-cream machines including those for use in refrigerators and freezers, ice-makers incorporating a motor-compressor and ice-makers intended to be incorporated in frozen food storage compartments, illuminated freezers, illuminated ice cream cabinets, illuminated refrigerators, incineration electric toilets, induction hobs, instantaneous water heaters, ironers, ironing machines, ironing presses for one-person operation, juice extractors, kettles, kettles and generators, kneaders, knife sharpeners, knives, lawn mowers, lawn trimmer and edgers, liquid heaters, liquid or food blenders, liquid-filled radiators, machines used for washing food, mangles, meat choppers, meat patty forming machines, meat saws, meat slicers, meat tenderizers, microscope projectors, microwave ovens, milk heaters, mincers, mixers, motor driven blenders, motor-compressors, motorized cleaning heads and current-carrying hoses associated with a particular vacuum cleaner, nonrefrigerated display cases, noodle makers, noodle strip cutters, opaque projectors (episcopes), opaque-transparency projectors (epidiascopes), operators and systems of doors gates draperies and louveres, outdoor electric barbecues, outdoor electric grills, oven /broilers, ovens, panel heaters, pasta mixer-extruders, pastry rollers, peanut grinders, pedestal fans, peelers, pendant ceiling fans, permanently connected appliances for household and commercial use, pizza ovens, popcorn machines, portable domestic ironing machines, portable heating tools and similar appliances, portable ovens, portioning machines, potato peelers, poultry saws, poultry water heaters, pressure cookers, projectors and similar appliances, pumps for garden ponds, pumps for liquids having a temperature not exceeding 35 degrees Celsius, pyrolytic self-cleaning ovens, raclette grills, radiant grills, radiant heaters, range hoods, rangettes, recessed freezers, recessed refrigerators, refrigerant condensers, refrigerant driers, refrigerant evaporators, refrigerant filters, refrigerant heat reclaimers, refrigerant recovery

/recycling machinery, refrigerant strainers, refrigerated beverage dispensers for use in commercial establishments designed for freestanding use or for building into fixtures, refrigerated bottle type beverage coolers, refrigerated display cases, refrigerated kitchen units, refrigerated meat, dairy or frozen food cases, refrigerated reach-in cabinets, refrigerated wall cabinets and bottle type beverage coolers, refrigerating appliances and ice-makers for use in camping touring caravans and boats for leisure purposes, refrigerating appliances for household and similar use, refrigeration equipment, refrigerators, refrigerators for use in recreational vehicles, rice cookers, roasters, room air conditioners, room heaters, rotary grills, rotary ironers for one-person operation, rotary rack ovens, rotisseries, rug shampooers, sandwich stations, sandwich toasters, sauna heating appliances, saws, self-service freezers, self-service ice cream cabinets, self-service refrigerators, series safety of household and similar electrical appliances, sewing machines, shredders, sieving appliances, slicers, slicing appliances for beans, slicing appliances for bread, cheese, meat, and the like, slide projectors (diascopes), slide-sorting appliances, slow cookers, sludge pumps, sludge-suction appliances, spin extractors, spiral type dough mixers, spring-driven clocks with an electrically operated winding mechanism, stationary circulation pumps for heating and service water installations, stationary cooking ranges hobs ovens and similar appliances, stationary domestic ironing machines, stationary griddles, stationary grills, steam cookers, steam humidifiers, steam irons, steam ovens, steam-convection ovens, sterilizers, still viewers, stock water heaters, storage water heaters, stoves, submersible pumps, suitcase fans, surface-cleaning appliances employing liquids, table ovens, teakettles, tenderizers, the cooking section of kitchen units which consists of various combinations of electric range surface units an oven a sink and a refrigerated cabinet, thermal storage room heaters, tilting braising pans, tilting kettle, tilting skillets, tin openers, toaster oven broilers, toaster ovens, toasters, trouser presses, tubular heaters, tumble dryers, tureens, unit coolers, upholstery shampooers, urns, utensil warmers, utility fans, vacuum cleaners, vacuum cleaners and water-suction cleaning appliances, vacuum cleaners for animal grooming, vacuum cleaning machines, vaporizers, vegetable cutters, vegetable dicer, vegetable slicer, vegetable steamers, vertical wet pit pumps, waffle irons, walk-in coolers, wall insert ventilating-type fans and ventilators, wall-hung freezers, wall-hung refrigerators, warming bin/griddle station, warming plates, warming trays, wash boilers, washing machines, water coolers, pressure or bottle type, freestanding or wall-mounted, having added features such as a means for heating water or a refrigerated space, water coolers, water distillers, water heaters (other than the storage type), water softeners and demineralizers, water-bed heaters, water-injection humidifiers, wet and dry vacuum cleaners including power brush for industrial and commercial use, window fans, yoghurt makers, electric floor surfacing and cleaning machines namely, cord-

connected floor cleaning machines, motor-operated floor cleaning machines, cord-connected floor surfacing machines, motor-operated floor surfacing machines, commercial and industrial floor polishing machines, commercial and industrial floor scrubbing machines, commercial and industrial sanders grinders or other types of surfacing machines of the hand-propelled or self-propelled type, rug scrubbers and shampooing machines, electric washing machines namely, electrically operated clothes-washing machines, electrically operated dishwashing machines, combination washing and drying machines, cord-connected and permanently connected machines for use in domestic or commercial locations and includes machines provided with coin- or ticket-operated mechanisms, conventional wringer machines, tumbler, agitator and spinner machines, combination washer-dryers, extractors of the centrifugal type and dishwashing machines of the rack and conveyor type, vacuum cleaners blower cleaners and household floor finishing machines namely, household commercial and coin-operated vacuum cleaning machines and blower cleaners intended for indoor or outdoor use or both, household commercial and coin-operated wet pick-up dry pick-up permanently mounted portable and central vacuum cleaners and blower cleaner systems, household current-carrying hoses for dry pick-up indoor use, household accessory electrified wall valves for central vacuum cleaning systems for connection of current-carrying hose/motorized nozzle combinations, household electrically powered floor finishing machines including floor polishers floor scrubbers floor sanders rug shampooers rug and floor washers and similar machines, floor treatment and floor cleaning machines for industrial and commercial use namely, electrical motor-operated floor polishing (including waxing and buffing) appliances namely, electrical motor-operated scrubbing appliances, electrical motor-operated grinding appliances, electrical motor-operated scarifying appliances, electrical motor-operated carpet shampooing appliances, spray extraction appliances for industrial and commercial use namely, electrical motor-operated spray extraction appliances and electrical attachments employing water-based cleaning agents for cleaning fabrics upholstery carpets floor coverings or hard surfaces intended for industrial and commercial use; business equipment namely, cabinets, chairs, desks, diskettes, letter openers, mini sorters, staplers; air-jetted bathtubs with pressure sealed door and drainage tank, bathtub /whirlpool bathtubs with pressure sealed doors, bathtubs (air jet), cast iron pedicure footbath, diverter valves (pool /spa), fibreglass reinforced plastic shells for whirlpool bathtubs(acrylic), hydromassage bathtub appliances, hydromassage bathtubs, pipe-less whirlpool bathtub appliances, plastic pedicure footbath, pool fittings (main drains sumps grates & anti vortex covers), safety suction valves, spa shell (tile lined FRP), spas (portable), spas /spa shells (acrylic), suction fittings, suction fittings (special use), therapy spas, whirlpool bathtub with pressure sealed door and drainage tank, whirlpool bathtubs, whirlpool bathtubs (acrylic), whirlpool bathtubs

with air jet, whirlpool bathtubs with pressure sealed doors, whirlpool bathtubs with water fill through the whirlpool piping systems, whirlpool piping systems (PVC, ABS & copper); miscellaneous apparatus namely, main junction boxes, electric, gas, and fluid flow metering equipment, switching and metering centres, line isolation monitors, current transformers, demand meters, subfeed meter sockets, test switches, electronically operated valves, general purpose valves, safety valves, valves intended to be incorporated into equipment, electrically powered mechanisms that are designed to provide the signals needed for monitoring valve operation from a remote location, electrically powered valve actuators, amplifier mikes, analogue tuners, antenna amplifiers, audio amplifiers, CRT, digital converter boxes, digital tuners, equalizer, LCD display, plasma displays, projection TVs, radio tuners, tape recorders, TV-FM amplifiers, VCR, video cassette players, video displays, accessory cabinets, accessory converter units, accessory cut label heads, accessory finishers, accessory general enablement kits, accessory mini-bases, adaptor stands, agent sets, aesthetic delivery apparatus, automatic choppers, automatic input stations, auxiliary contact blocks, auxiliary units, bank proof machines, blood drawing apparatus, bonding connectors, cabinet assemblies, cabinets and cutout boxes, cellular metal floor raceways and fittings, central systems, coin mechanisms, coin operation interfaces, coin-ops, composers, conditioners, console tables, contact cartridges, contact elements, conversion feature kits, conversion kits, CPO cabinets, CPS consoles, CRT stands, cylinder lock push button contact blocks, datasets, door, door panel assemblies, double insulated snow movers, drum cavity temperature kits, drum heater kits, dual lens, dual pocket modules, dual remote scanners, electric boilers, electric fans, electric ranges, electroencephalograph, electronize memory systems, electrostatic discharge grounding testers, enclosures for industrial control panels, endorser modules, endoser /pockets, endoser-bank stamps, enhanced networks, entry level systems, external contact block, fan relay, field conversion kits, field installed accessories, field installed upgrade packages, file storage cabinets, film image recorders, flat conductor cable-fittings, floor terminals, foreign accessory kits, foreign attachment kits, foreign interface kits, Forms-tackers, four pocket modules, freestanding delays, front end cabinets, fusers, gate, heat pump pool heaters, high humidity kits, Holgun, humidistats, illuminated operator, image output terminals, immunoanalysers, industrial control panels, infant radiant warmer beds, input stations, inscribers, inserter folders, installation kits, internal auxiliary contact block, interpreters, inventory recorders, jack assemblies, leakage monitor, leakage rated dampers, ledger feeders, ledger units, listed conversion units namely matrix board cooling kits, listed field installed accessories, louver and window operators and systems, lower limb flexors, lower limb positioner, lower limb units, magnetic stripe cards, magnetic tape units, magnetically operated control switches, mailers, manhole rungs, marine blowers, marine

motor controllers, marine shipboard cable, marine shore power inlets, marine type lighting fixtures, massage and exercise machines, memory cabinets, micro power II, mineral insulated metal sheathed cable and fittings, mini data racks, mobile storage systems, modular checkout centers, modular communication systems, modular wands, modules, motor drives, motor operators, muscle stimulators, non-impact endersers, non-reduction processors, orbital, outdoor telephone booths, output sorters, oxidation retardant greases and lubricants, packet switching cabinets, perforator accessories, pocket modules, power files, proof inscribers, protocol retail terminals, proximity switch, punches, push-pull buttons, rackmounts, reciprocating, relaxers, retractor positioner, retrofit kits, reversing starters, room thermostats, scoring readers, second sorter enable kits, slitter/perforators, small branch processors, solid state control systems, solid state time delay relay, sorter systems, sorter-readers, sorters, sorters/finisher modules, speech boxes, stand-up handles, storage arrays, store systems, swimming pool and spa equipment, synchronous communication Y-boxes, synchronous intercouplers, system fail transfers, system memories, system, tag test table, tape control units, tape converters, tape units, temperature controllers, test sets, thermostats, transfer posters, two speed starters, ultraviolet inspection lamps, underfloor raceways and fittings, upper limb positioner, validators, washing machines for parts, water-cooling towers, wound drainage apparatus, wound suction apparatus, microscope projectors; elevator equipment namely, controllers, machines, operators and indicators, elevator duty contactors, door & gate locking devices, escalator braking systems, elevator oil buffers, lifting devices for handicapped, elevator duty hydraulic valves and other miscellaneous apparatus; motor controllers namely, auxiliary devices incorporated as an integral part of the units, brushless motor controllers, combination contactor units, control and protective devices and accessory devices for starting, stopping, regulating, controlling or protecting electric motors, generators, heating apparatus or other equipment used to control an industrial process, control circuit, control circuit fuses, control devices intended for heating, control devices intended for lighting, control transformers, dead-front switchboard, distribution panelboards, electric pump motor controllers, electrical controllers for diesel engines, electromechanical contactors, enclosed panelboards, feeder-tap units, float-operated switches, flow-operated switches, full-voltage multispeed combination motor control units, full-voltage non-reversing combination motor control units, full-voltage reversing combination motor control units, incoming-line equipment such as circuit-breaker, incoming-line equipment such as fusible switch, incoming-line equipment such as isolation switch, incoming-line equipment such as main lugs, indicating lights, industrial control equipment, lighting panelboards, lighting transformers, magnetic overload relays, magnetic starters, manual controllers, manual starters, motor control centres, pressure-operated switches, proximity switches, push-

button stations (including selector switches and pilot lights), pushbuttons, reduced-voltage part-winding wye-delta or auto-transformer combination motor control units, relays, resistors, resistors intended for heating and lighting including those for motor generator fields, rheostats, rheostats intended for heating and lighting including those for motor generator fields, selector switches, series low-voltage controlgear, series low-voltage switchgear, solid-state industrial controllers such as adjustable-speed drives, solid-state industrial controllers such as programmable controllers, solid-state industrial controllers such as protective relays, special equipment assemblies, stepper motor controllers, switchboards, switches, thermal overload relays, time-delay relays, time-delay switches, vacuum-operated switches, solid-state speed controls namely, solid-state speed controls used in circuits for the control of shaded motors and other motors suitable for use with this type of control, solid-state speed controls used in circuits for the control of pole motors and other motors suitable for use with this type of control, solid-state speed controls used in circuits for the control of permanent motors and other motors suitable for use with this type of control, solid-state speed controls used in circuits for the control of split motors and other motors suitable for use with this type of control, solid-state speed controls used in circuits for the control of capacitor motors and other motors suitable for use with this type of control, solid-state speed controls used in circuits for the control of universal motors and other motors suitable for use with this type of control, controls intended for flush mounting, controls intended for use as a table-mounted control to which a portable motor can be temporarily connected, controls intended for installation in other equipment as part of the control package for that equipment, controls intended for permanent installation in the supply line of a motor, controls intended for other similar applications within the general outline above, fire pump controllers namely, controllers intended for starting and stopping centrifugal and positive displacement fire pumps, including automatic and non-automatic types for electric motor with or without transfer switch or engine driven pumps, electromechanical motor-starters namely, contactors associated with overload, short-circuit protective devices, starters associated with separate short-circuit protective devices and/or with separate short circuit and integrated overload protective devices; contactors or starters combined under specified conditions with their own short-circuit protective devices, combination starters, protected starters, circuit-breakers units used as short-circuit protective devices, fuse-combination units used as short-circuit protective devices, process control equipment namely, analogue equipment such as indicating, integrating, and recording instruments with or without a control function, digital equipment such as indicating, integrating, and recording instruments with or without a control function, transmitters, transducers, analyzers, telemetry equipment, programmable controllers; programmable controllers namely, controllers and associated peripherals for measurement recording and

control of process detectors indicators integrators recorders analyzers transmitters transducers telemetry signal processors, electric generators, electric lamp control equipment, electric motors, electronic volume correctors, electronically corrected meters, fan motor speed controls, logic relay controller, magnetic motor controller, magnetically operated control switches, magnetically operated overload relays, magnetically operated switches, may be similar components for installing in other electrical equipment, sensors for temperature pressure pH flow rates humidity volume size capacitance light levels; industrial control assemblies namely, control and protective devices and accessory devices for starting, stopping, regulating, controlling or protecting electric motors, generators, heating apparatus or other equipment used to control an industrial process, control circuit, control devices intended for heating, control devices intended for lighting, enclosed panelboards, float-operated switches, flow-operated switches, high-voltage full-load interrupter switches, high-voltage isolating switches, magnetic overload relays, magnetic starters, manual controllers, manual starters, medium-voltage ac contactors, medium-voltage ac control centres, medium-voltage ac controllers, pressure-operated switches, proximity switches, push-button stations (including selector switches and pilot lights), relays, resistors, resistors intended for heating and lighting including those for motor generator fields, rheostats, rheostats intended for heating and lighting including those for motor generator fields, switch control assemblies and control panels for industrial processes, thermal overload relays, time-delay relays, time-delay switches, vacuum-operated switches, panelboards for service entrance use namely, custom-built panelboard assemblies, synthetic fuses to be used in the simulated load cycle test on fusible panelboards, process control equipment, analogue equipment such as indicating, integrating, and recording instruments with or without a control function, digital equipment such as indicating, integrating, and recording instruments with or without a control function, transmitters, transducers, analyzers, telemetry equipment, programmable controllers, process control equipment namely, analogue equipment such as indicating, integrating, and recording instruments with or without a control function, digital equipment such as indicating, integrating, and recording instruments with or without a control function, transmitters, transducers, analyzers, telemetry equipment, programmable controllers, switchgear assemblies namely, interrupting devices, air circuit breakers, power circuit breakers, control metering protective and regulating equipment with associated interconnections and supporting structures; switches namely, automatic temperature switches, automatic transfer switches, bypass transfer switches, closed transition transfer switches, cut-out switches, cylinder lock selector switches, dead-front switches, electrical temperature regulators, enclosed switches, float-controlled switches, foot switch assemblies, foot switch kits, foot switches, fused molded-case switches, hybrid transfer switches, industrial control

equipment float-operated switches, industrial control equipment pressure-operated switches, industrial control equipment switches, industrial control equipment time-delay switches, industrial control equipment vacuum-operated switches, isolating transfer switches, level regulators, manual transfer switches, micro-switches, molded-case switches, pressure regulators, relays, remote-control switches, reversing switches, rotatable selecting switches, short-time switches, small switches, staircase switches, stepping relays, stepping switches, switches and relays controllable by current pulses, switches pressure switches, time relays, time switches, timers, transfer switches for fire pumps, switches for appliances namely, switches (mechanical or electronic) for appliances actuated by hand by foot or by other human activity to operate or control electrical appliances and other equipment for household or similar purposes, general-use snap switches namely, ac/dc fixture switches, ac/dc rated switches, pendant and through-cord switches, self-contained switches, single-pole momentary-contact door switches, switches constructed to be installed readily in a flush device box and intended for connection to branch-circuit wiring, switches constructed to be installed readily in an outlet-box cover and intended for connection to branch-circuit wiring, switches intended for surface mounting, clock-operated switches namely, clock-operated switches completely enclosed plug-in or cord-connected, clock-operated switches may be incompletely enclosed, clock-operated switches may be restricted in performance capabilities for use in other equipment, time switches namely, timers and time switches for household and similar use that may use electricity, gas, oil, solid fuel, solar thermal energy etc. or a combination thereof including heating air conditioning and similar applications; lighting namely, air-handling luminaires, alarm lights, aquarium hoods, auto-transformers, cabinets (illuminated bars, hutches etc), chain-supported type of portable luminaires, colour wheels, control transformers, decorative-lighting strings, desk lamps, direct plug-in nightlights, display types, drafting lamps, electric luminaires for indoor use, electric luminaires for inground use, electric luminaires for outdoor use, electrical control systems for lighting systems, electronic (flashing touch-control) portable luminaires, Egress path marking luminaires, extension hand-lamps, extra-low-voltage lighting systems, extra-low-voltage landscape lighting systems, fibre-optic portable luminaires, flexible-cord-supported type portable luminaires, floodlights, floor lamps, fluorescent lamp type fixtures, fluorescent lamps, garden lights, gimbal lights, glow-starters for fluorescent lamps, high intensity discharge lamp type lighting fixtures, high-intensity discharge (including cold-cathode and low-pressure sodium) lamps, hook-supported types of portable luminaires, hospital lamps, illuminated forms or shapes (figurines fire logs terrestrial globes plaques etc) portable luminaires, incandescent lamp type lighting fixtures, incandescent lamps, isolating transformers for general use, kits, lamp testers, lampholder fittings, LED luminaires, light bulbs, light channels for display purposes, lighting

ballasts, lighting diffusers and, lighting fixtures, lighting fixtures and fittings, luminaires for and film studios (outdoor and indoor), luminaires for road and street lighting, luminaires for stage lighting (outdoor and indoor), luminaires for television studios (outdoor and indoor), luminaires with built-in transformers for filament lamps, machine-shop lamps (eg illuminated shields for use with electric grinders), make-up mirrors, medium-screwbase incandescent lamps, neon transformers and power supplies, novelty lamps, nursery lamps, photo and film luminaires, picture lamps, pilot light units, planter lamps, plug-in night-lights, pole lamps, portable child-appealing luminaires, portable electric hand lamps, portable fluorescent luminaires for decorative purposes, portable fluorescent luminaires for illuminative purposes, portable incandescent luminaires for decorative purposes, portable incandescent luminaires for purposes, portable lamps, portable luminaires, recessed luminaires, retrofit kits, rope-supported type of portable luminaries, safety isolating transformers, self-ballasted lamps and lamp adapters, series luminaires, series safety specifications for incandescent lamps, shaver transformers and shaver supply units, special purpose lighting fixtures, steel-cable-supported type of portable luminaries, submersible luminaires, swimming-pool luminaires accessories, table lamps, transformer-operated ultra-violet hobby lamps, tungsten filament lamps for domestic and similar general lighting purposes, tungsten halogen lamps for domestic and similar general lighting purposes, wall (pin-ups under-cabinet) lamps, equipment for use with electric discharge lamps namely, ballasts of the electronic (solid state) types for use with fluorescent lamps, ballasts of the reactance types for use with fluorescent lamps, ballasts of the resistance types for use with fluorescent lamps, ballasts for use with high-intensity electric discharge lamps of the metallic vapour types including low-pressure sodium and similar types, submersible and swimming pool luminaires accessories namely, portable incandescent luminaires of the swimming-pool type and of the submersible type intended for use in other than swimming pools, portable electric-discharge-lamp (fluorescent mercury- and sodium-vapour) luminaires of the swimming-pool type and of the submersible type intended for use in other than swimming pools, stationary incandescent luminaires of the swimming-pool type and of the submersible type intended for use in other than swimming pools, stationary electric-discharge-lamp (fluorescent mercury- and sodium-vapour) luminaires of the swimming-pool type and of the submersible type intended for use in other than swimming pools, wet-niche type of swimming-pool luminaires, dry-niche type of swimming-pool luminaires, forming shells for use with wet-niche luminaires, deck boxes complete with covers for installation, glass panels and the necessary mounting and sealing frames and gaskets for preventing the pool water from entering a dry niche; and, metal guards which may be provided for mechanical protection of glass panels and for the reduction of the electric field that may be established in the water of the pool as a result of electrical faults that may develop in the luminaire, unit equipment for

emergency lighting namely, exit signs, emergency luminaires, central power systems for emergency lighting, stage luminaires and studio luminaires namely, stationary incandescent stage luminaires, stationary incandescent studio luminaires, portable incandescent stage luminaires, portable incandescent studio luminaires, stationary gaseous discharge stage luminaires, stationary gaseous discharge studio luminaires, portable gaseous discharge stage luminaires, portable gaseous discharge studio luminaires, safety requirements for electronic flash apparatus for photographic purposes namely, apparatus of the single-flash type which can have more than one flash head operating at the same time, apparatus for the illumination of sequential photographic exposures, battery chargers and supply units to be used in connection with electronic flash apparatus for photographic purposes. these auxiliary units may form a part of the mains plug, accessories such as light regulators and slave units specified in the instruction leaflet, mains-operated apparatus, battery-operated apparatus, apparatus having a combination of mains and battery supply, electrical supply track systems for luminaires namely, track systems designed for ordinary interior use for mounting on or flush with or suspended from walls and ceilings, ballasts for tubular fluorescent lamps namely, complete ballasts and to their component parts such as reactors transformers, complete ballasts and to their component parts such as capacitors, ballasts for discharge lamps (excluding tubular fluorescent lamps) namely, ballasts for discharge lamps such as high-pressure mercury vapour, low-pressure sodium vapour, high-pressure sodium vapour, and metal halide lamps, starting devices (other than glow starters) namely, starting devices (starters and ignitors) for tubular fluorescent and other discharge lamps, a.c. supplied electronic ballasts for tubular fluorescent lamps, self-ballasted lamps for general lighting services, capacitors for use in tubular fluorescent and other discharge lamp circuits, general-purpose luminaires namely, general purpose luminaires for use with tungsten filament lamps, general purpose luminaires for use with tubular fluorescent lamps, general purpose luminaires for use with other discharge lamps, portable luminaires for garden use namely, portable pedestal luminaires, handlamps namely, handlamps which can be fixed to a support by means such as a wing screw clip or magnet, luminaires such as those used for inspection of the interior of barrels, luminaires for swimming pools and similar applications namely, fixed luminaires intended for use in water or in contact with water in for example the basins of swimming pools fountains paddling pools and garden pools, lamp controlgear namely, a.c. supplied electronic ballasts for fluorescent lamps, power transformers and power supply units namely, stationary or portable single-phase or polyphase air-cooled (natural or forced) isolating and safety isolating transformers, stationary or portable single-phase or polyphase air-cooled (natural or forced) separating transformers auto-transformers variable transformers and small reactors, separating transformers for general use namely, stationary or portable single-

phase or polyphase aircooled separating transformers, solid-state lighting controls namely, solid-state lighting controls for incandescent lamps; solid-state lighting controls for the control of fluorescent hid ballasted and similar lamps, controls intended for use in installations as a flush-mounted device, controls intended for use in installations as a surface-mounted device, controls intended for use as a table-mounted unit to which portable luminaire(s) can be temporarily connected, controls intended for use in installations or devices where controls form or are part of a whole system, controls intended for installation in a lamp holder, controls intended for permanent installation in the supply line of a lamp, controls intended for direct plug-in devices, controls intended for other similar applications, solid-state dimming controls namely, dimmers, touch dimmers, lampholders namely, cover holders and connectors for electric lamps including incandescent fluorescent and other electric-discharge-type lamps, screw lampholders, holders for automatic starters, holders for fluorescent self-ballasted lamps and fluorescent lamp adapters with mating pin bases, lampholder inserts, indicator lamps, naval-use lampholders; measuring equipment namely, accelerometers, analyzers, combustible gas, toxic gas, oxygen depletion, carbon monoxide and hydrogen sulfide detector, detectors, displacement sensors, electrolytic sensors, gas detector, gyroscopes, inclinometers, indicators, integrators, magnetometers, orientation sensors, recorders, sensors for temperature, pressure, pH, flow rates humidity, volume, size, capacitance, light levels, signal processors, straightness testers, telemetry, toxic gas and oxygen depletion detector, transducers, transmitters may be similar components for installing in other electrical equipment signal generators, power supplies, transducers, transmitters; motors and generators namely, AC machines (including universal motors), automotive motors, DC machines (including universal motors), generators, household generators, household motors, industrial generators, industrial motors, inverter-duty AC machines, motors, portable generators, standby generators, motors with inherent overheating protection namely, ac and dc motors with inherent overheating protection, motors with protective devices that are responsive to motor temperature alone, motors with protective devices that are responsive to motor temperature and motor current passing through the device, emergency electrical power supply for buildings namely, emergency generators and associated equipment, power supplies with extra-low-voltage class 2 outputs namely, power supplies including transformer units of both the direct plug-in and cord-connected types that utilize a step-down isolating transformer of the extra-low-voltage secondary type and that may incorporate rectifiers and other components to provide an ac or dc output, battery chargers for rechargeable batteries, manually operated generator transfer panels namely, manual transfer panels; scales namely, body weight scales, digital scales, industrial scales, kitchen scales, scales for commercial use; service equipment namely,

combination service entrance equipment namely, panelboards for service entrance use, service-entrance feeder busway, service-entrance feeder associated fittings; service and metering equipment namely, meter-mounting devices, indoor and outdoor meter-mounting devices either as complete self-contained devices or provided as a part of service equipment, meter-mounting devices, transformer-rated meter-mounting devices; sign accessories namely, brochures, electrical control systems for lighting systems, light bulbs, lighting ballasts, lighting diffusers, lighting fixtures, lighting poles namely, free-standing poles of ferrous, metal, aluminum, concrete and wood and their accessories for use in the support of lighting equipment, poles used for the support of lighting equipment such as luminaries electric signs and traffic lights, poles used for to support electric signs, poles used to support traffic lights, poles as supports for aerial conductors used to supply the lighting equipment, concrete or metal poles providing wireways for conductors entering the poles, portable and stationary electric signs and displays namely, signs having outline lighting wherein the sources of light is incandescent lamps, signs having outline lighting wherein the sources of light is fluorescent lamps, signs having outline lighting wherein the sources of light is high-voltage luminous discharge tubes including neon tubes, signs having outline lighting wherein the sources of light is high-intensity discharge lamps; sprayer accessories namely, accessory handles, air compressors and vacuum pumps for painting equipment, hand tools for servicing and repairing paint sprayers, holders for spare spray nozzles, hose clips, hoses, motorized nozzles, paint containers, siphon hose holders, tool boxes, tool pouches, turbine nozzles; toys namely, battery charger for toys, battery operated toys, children's toys, construction toys, crib toys, drawing toys, electric cat toys, electric dog toys, electric games, electric music box toys, electric pet toys, electric toy airplanes, electric toy bakeware and cookware, electric toy banks, electric toy oven, electrical toys including radio controlled toy electric motor driven toys or electric vibrator operated toys, electrically illuminated drawing tables, fantasy character toys, infant development toys, plush toys, power supplies for toys; pull toys, toy cotton candy makers, toy electric scooters, toy still picture projectors, toy watches; miscellaneous heaters namely, aquarium heaters, bed heaters, heat pump water heaters, heaters for vehicles, kerosene heaters, portable electric heaters, propane heaters, solar water heaters, storage tank water heaters, swimming pool heaters, tankless water heaters, electrically heated hobby and educational type kilns, electrically heated warming pads namely, single-heat single-speed warming pads, multi-heat warming pads, single-heat multi-speed warming pads, electrically heated bedding appliances for household use namely, cord-connected electrically heated blankets, cord-connected electrically heated comforters, cord-connected electrically heated quilts, cord-connected electrically heated sheets, cord-connected electrically heated mattresses, cord-connected electrically heated and mattress pads, engine heaters and battery warmers

namely, internal and external coolant immersion heavy duty engine heaters, internal and external oil immersion heavy duty engine heaters, external surface heavy duty engine heaters, industrial heating equipment namely, portable industrial type heating equipment, stationary industrial type heating equipment, electric air-heaters namely, permanently connected air-heaters for household commercial and industrial use, cord connected air-heaters for household commercial and industrial use, convection air-heater, forced air air-heater, radiation air-heater, ceiling types air-heater only or in combination with either lighting or ventilating components or both, liquid-filled radiator air-heater, heater elements namely, open wire heater element (including wire ribbon and expanded metal), metal sheathed heater element (including removable-type range surface and grounded plug-in type), variable resistance /temperature heater element (VR/T), special heater element (e.g. quartz tube woven mat parallel circuit mat rope cartridge and strip), electric furnaces in combination with solid fuel-fired furnaces namely, central warm air electric resistance type furnaces; insulating devices and materials namely, foam paper and fabric in the form of panels and sheets and tubes; receptacles namely, electrical communication receptacles, receptacles for communication systems, plugs for communication systems, connectors for communication systems, connectors for communication systems intended to electrically terminate communication cord sets, connectors for communication systems intended to electrically terminate communication cords, connectors for communication systems intended to electrically terminate equipment that is connected to an exposed communication plant or connected to a telecommunication network, plugs for communication systems intended to electrically terminate communication cord sets, plugs for communication systems intended to electrically terminate communication cords, plugs for communication systems intended to electrically terminate equipment that is connected to an exposed communication plant or connected to a telecommunication network, receptacles for communication systems intended to electrically terminate communication cord sets, receptacles for communication systems intended to electrically terminate communication cords, receptacles for communication systems intended to electrically terminate equipment that is connected to an exposed communication plant or connected to a telecommunication network; flexible connectors namely, flexible metallic water connectors, flexible waste system, flexible water connectors, flexible water connectors (stainless steel), flexible water connectors with excess flow shutoff device, flexible water fixture connectors (PVC); plastics, namely, plastic materials plastic pipe and components (including metal components) used with such namely, ABS-DWV pipe, ABS-DWV pipe & fittings, ABS-DWV pipe (cellular core), acrylic material, barrier materials, closet rings (ABS), closet rings (PVC), cold -expansion fittings for PEX pipe, corrugated PE tubing, CPVC hot & cold water distribution system, CPVC hot & cold water fittings, CPVC hot & cold

water pipe & tubing, CPVC hot & cold water pipe fittings, CPVC pipe and fittings for limited chemical waste drainage systems, CPVC solvent cements, CPVC solvent cements (One Step), crimp style brass/copper fittings for joining PE-AL-PE or PEX-AL-PEX tubing, cross-linked polyethylene (PEX) tubing, cross-linked polyethylene water distribution system (PEX), domestic thermoplastic waste tube & fittings (ABS PP PVC), DWV fittings - miscellaneous (ABS & PVC), DWV fittings - miscellaneous (ABS & PVC) (Classified Listing), DWV internal cleanout fittings, maintenance and utility boxed hydrants, mechanical couplings for (PE) piping, mechanical couplings for polyethylene piping, mechanical couplings using thermoplastic elastomeric (TPE) gaskets for joining DWV sewer sanitary and storm plumbing systems for above and below ground use, metal insert fittings utilizing a copper crimp ring for SDR 9 cross-linked polyethylene (PEX) tubing, metal insert fittings utilizing a copper or copper alloy crimp ring for SDR 9 cross-linked polyethylene (PEX) tubing, non-pressure water hose & tubing, outlet boxes (laundry & misc.), outlet boxes (washing machine), outlet boxes (washing machine/ice maker/tub box), PE-AL-PE composite pressure pipe system, PEX tubing, PEX tubing (SDR 9) with factory applied aluminum and polyethylene coating, PEX-AL-PEX composite pressure pipe system, pipe alignment & secondary support systems, pipe couplings & fittings, pipe couplings adapters & stoppers (synthetic, rubber & stainless steel), pipe joint compounds, pipe sleeves, pipe wrap tapes, plastic insert fitting utilizing copper crimp ring for PEX tubing, plastic mechanical fittings for use on polyethylene gas pipe and tubing, poly vinyl chloride (PVC) cold water gripper fittings, poly vinyl chloride (PVC) plastic pipe fittings schedule 80, polyethylene cold water pipe, polyethylene sleeved-corrugated stainless steel tubing for use in fuel gas piping systems, polypropylene injection and extrusion materials, poly vinyl chloride (PVC) plastic pipe fittings schedule 40, polyvinylidene fluoride corrosive waste drainage systems, PP-R/AL/PP-R composite pressure pipe and PP-R fitting system, pressure rated polypropylene piping system, primers for PVC and CPVC, primers for PVC Piping Systems, PVC cold water compression fittings, PVC cold water pipe, PVC cold water pipe (elastomeric gasketed), PVC cold water pipe (ultra-violet resistant), PVC cold water schedule 40, PVC or ABS covers for use with unshielded flexible transition couplings for underground piping systems, PVC plastic pipe (Sch. 40 80 120), PVC solvent cements, PVC solvent cements (one step), PVC well casing pipe, PVC-DWV fittings, PVC-DWV pipe (cellular core), PVC-DWV pipe and fittings, rigid poly vinyl chloride(PVC) compound, sewer fittings (PVC), sewer fittings (solvent cemented)(PVC), sewer pipe & fittings (PVC), sewer pipe (PVC), sewer pipe compound, smooth wall polyethylene (PE) pipe, solvent cement for ABS plastic pipe and fittings, solvent cements, solvent cements for PVC plastic piping systems, solvent cements for transition joints between ABS & PVC non-pressure piping systems, thermoplastic gas pipe tubing and/or fittings; plumbing accessories, namely, wastes drains and

cleanouts namely, ABS and PVC roof drains, ABS cleanout fittings, ABS PVC and cast iron DWV Test fitting with integral cleanout, bath waste and overflows assemblies cleanout/test caps, cleanouts, cleanouts (cast iron), drain, drain tailpiece insert, drain tube, drains (floor), drains for prefabricated and precast showers fittings, DWV drain connectors, fittings - termination floor and general purpose drains with metal, floor drain trap seal protection devices, floor drain with integrated bonding flange, floor sinks (enameled cast iron), floor sinks (epoxy coated cast iron), floor sinks (PVC), floor sinks/drains lavatory, roof drains, roof drains with integral overflow drain, roof flashings, roof flashings - material composition, roof/deck drains (copper), shower drains, shower drains (ABS & PVC), shower drains (brass), shower trench drain, sink tailpiece drain coupling, siphonic roof drains, stainless steel floor sinks, subdrains for built-up shower pans, subdrains for built-up showers, trap primer valves, trap primers, trap primers - multiport (electronic), trap seal primer devices - drainage types and electronic design types, trap seal primers valves, trap with cleaning device, water saver p-trap/trap primer, backflow preventers and backwater valves namely, assembly vacuum breakers (atmospheric), backflow preventer, backflow preventers (double check), backflow preventers (faucets), backflow preventers (hose bibb), backflow preventers (reduced pressure), backflow preventers and relief valves, backwater valves, backwater valves & adapter fittings (DWV-sewer), backwater valves (ABS & PVC), backwater valves (cast iron), dual check backflow preventers (hose bibb), pressure vacuum breaker, vacuum breakers (backflow), vacuum breakers (pressure type), vacuum breakers (spill resistant pressure air gaps (dishwasher waste), valves namely, ball valves, brass ball valves, bronze gate globe angle and check valves, cast iron pipe gaskets (neoprene), chemical dispensing systems, earthquake actuated automatic gas shut-off valves, fixture stops, flow regulating device, freeze protection valves for use on backflow preventers pressure relief connection for dispensing equipment, sanitary waste valves potable water, self-sealing waterless waste valves, shut off devices with or without shower heads, stack air admittance valves, supply stop with excess flow shutoff device, supply stops, supply stops with integral water hammer arresters, temp. actuated flow reduction valves, temperature actuated mixing valves for hot water distribution systems, water flow shut-off devices, water hammer arresters, water heater relief valve drain tubes, water leak detection system, water pressure regulator, pipe and tubing [non-plastic] including components and materials associated with such namely, cast iron soil pipe, cast iron soil pipe and fittings, cast iron soil pipe and fittings (hubless), clamps (stainless steel), closet rings (cast iron), copper drainage tube (DWV), copper fittings, copper fittings (press type), copper pipe and tubing, copper tubing joined with structural adhesive fittings, copper water tube fittings, corrugated stainless steel tubing for fuel gas piping, couplings, couplings (shielded), dielectric fittings, dielectric pipe unions, elastomeric

elbows and tees for above ground, expansion couplings (thermoplastic rubber), fitting (elastomeric), fittings - ABS-DWV, fuel gas pipe copper fittings (press connect type), grooved mechanical pipe couplings & grooved end fittings, heavy duty shielded couplings, high pressure stainless steel shielded couplings for use with hubless cast iron pipe and fittings, hinge type plastic hubless couplings, hose (dishwasher waste), hubless cast iron pipe couplings, hubless pipe couplings (shielded and unshielded), hubless pipe couplings (unshielded), hubless pipe repair couplings (unshielded), insulated protectors (p-traps risers & supply stops), joining hubless cast iron soil pipe and fittings, joint DWV expansion, metallic fittings for use on gas SDR pipe & tubing distribution manifold, piston driven malleable cast iron fittings with mechanical press connections for steel pipe manually, push fit fittings, seamless red brass pipe shielded transition couplings, supply risers (vinyl & stainless steel), tubing - pressure tubing (radiant heating), tubular brass fittings, wrought copper and wrought copper alloy solder joint drainage fittings-DWV tubing, grease interceptors and collectors namely, automatic grease removal devices, FOG (fats oils and greases) disposal system, grease interceptors, grease removal device, grease trap, grease traps (bacteriological), oil/water separators and coalescing plate separators, ultra flow hydro-mechanical grease interceptors, tanks namely, septic tanks (fibreglass), septic tanks (polyethylene septic tanks (prefabricated), septic tanks (prefabricated), sewage holding tanks (directly mounted), waste water trim (ABS & PVC), waste holding tanks (ABS), waste holding tanks (polyethylene), wastewater interceptor system, water devices - air accumulator tank, water tanks, plumbing components (solar) namely, collectors (flat plate), collectors (pool spa & hot tub), heat exchanger within storage tank, integral collector storage (ICS), solar water heater, water heaters solar (thermosyphon), water treatment units namely, drinking water distillation systems, drinking water treatment chemicals, precipitators for water treatment units, residential cation exchange water softeners, reverse osmosis drinking water systems, swimming pool and spa - chlorine and bromine generators, ultraviolet microbiological - water treatment systems, UV purification equipment, liquid pumps namely, component-type pump units intended to be built into equipment, cord- and plug-connected pumps, cord-connected poolside pumps, extra-low-voltage recreational vehicle pumps, insulated wet end pumps, motor-operated liquid pump units, plug-connected poolside pumps, pool and spa cover drain pumps, pumps for e-cord-connection to the source of supply, pumps for permanent connection to the source of supply, submersible pumps; footwear namely, athletic footwear, chemical exposure protective footwear, children's footwear, exercise footwear, fire protective footwear, golf footwear, infant footwear, medical personnel footwear, orthopedic footwear, outdoor winter footwear, protective footwear, rain footwear, ski footwear, sports footwear; headwear namely, hardhats, helmets, protective headwear, motorcycle helmets; straps namely, D-rings straps, ratchet reducer coupling straps, tie-down

straps, towing straps; interior surfacing material namely, chemically pressure treated lumber and plywood, factory-assembled floor and wall panels used as components of mobile and modular homes, interior wall/ceiling panels investigated for flame spread rating only; sports safety equipment namely, braces, first-aid kits, general-purpose rope and, goggles, harness buckles, harnesses, personal flotation aids, sports helmets; safety glazing used on motor vehicles; domestic gas cooking appliance accessories namely, barbecue tool sets, cutting boards, food garnishing tools; miscellaneous domestic heaters namely, swimming pool heaters, storage tank water heaters, tankless water heaters, heat pump water heaters, solar water heaters; electrical equipment accessories namely, AC adaptors, accessories namely control boxes, accessory auditoron kits, accessory coin-op kits, accessory couplers, across-the-line starters, antenna amplifiers, appliance controls, appliance couplers for household and similar general purposes, audio terminals, auditorons, automatic alternator, auxiliary switch, battery cabinets, battery chargers, battery chargers, battery packs, busbars, cable concentrators, cable data collectors, cable sealing fittings, cable trays, channel banks, channel interface units, channel interfaces, channel servers, chargers, coil relay units, connectors, control panels and assemblies for use in hazardous locations, control units, controllers, controls, converters, cord connector bodies, cord sets and power supply cords, couplers, current carrying inlet valve assemblies, current limiter, current sensing relays, current taps, DC back up systems, dimmers, electric power supplies, electrical metallic tubing and fittings, electrical non-metallic tubing and fittings, electrical receptacles and outlets, electronic motor protection units, fluorescent ballasts, ground connector, ground fault detection relay, ground grid connectors, heat reclaimers, industrial control panels, industrial control panels are factory wired assemblies of industrial control equipment such as motor controllers switches relays and auxiliary devices the panels may include disconnect means and motor branch circuit protective devices, industrial control switches, insulated grounding bushings, insulating link, junction and pull boxes, lamp transformers, limited switches, line amplifier, line drivers, line expansion modules, liquid-tight flexible metal conduit, loop to ground start converters, low voltage power circuit protector, machine-operated switches, motor control centers are floor mounted assemblies of one or more enclosed vertical sections having a common horizontal power bus and primarily containing combination motor control units, optional extension cabinets, outlet boxes and fittings, outlet circuit testers, potentiometer units, potentiometers, power adaptors, power amplifier, power distribution center for communications equipment, power drives, power factor corrector units, power packs, power supplies, power unit equalizers, primary protectors for communication circuits, programmable communications adapters, quick connect terminals, rigid ferrous metal conduit, rigid nonferrous metallic conduit, schedule 40 and schedule 80 PVC plastic rigid non-metallic conduit, selector switch, solenoid voltage

testers, solenoids, splice connectors, switchboards, switches, tap and run connectors, temporary power taps, theatre dimmer controllers, thermal overload relays, thermal relays, transformer/relays, transient voltage surge suppressors, transmitters, underground feeder and branch circuit cable, undervoltage trip, uninterruptible power supplies, uninterruptible power supply equipment, voltage sensing relays, wired cabinets, battery chargers namely, portable battery chargers for indoor and outdoor use, mobile battery chargers for indoor and outdoor use, stationary battery chargers for indoor and outdoor use, fixed battery chargers for indoor use, battery chargers for special applications such as wheelchairs and other medical applications, marine battery chargers intended to be permanently installed on a boat, transformerless nonisolated battery chargers for charging special-purpose battery packs, uninterruptible power systems namely, movable uninterruptible power systems, stationary uninterruptible power systems, fixed uninterruptible power systems, built-in uninterruptible power systems, cutout boxes namely, non-metallic cutout boxes, metal cutout boxes, junction boxes namely, non-metallic junction boxes, metal junction boxes, pull boxes namely, metal pull boxes, non-metallic pull boxes, surface raceway systems namely, metal surface raceway systems, non-metallic surface raceway systems, non-metallic surface raceways, non-metallic surface raceway fittings, cellular metal floor raceways, cellular metal floor raceway fittings, cellular concrete floor raceways, cellular concrete floor raceway fittings, underfloor raceways and fittings, underfloor raceway fittings, tubular support members and associated fittings for domestic and commercial service masts, rigid PVC boxes and fittings namely, rigid PVC box fittings, rigid PVC junction boxes, rigid PVC conduit boxes, rigid PVC surface mounted device boxes, rigid PVC device box covers, rigid PVC blank box covers, rigid PVC expansion joints, rigid PVC junction box terminal adapters, rigid PVC female adapters, rigid PVC reducers, rigid PVC caps, rigid PVC bell ends, tray systems namely, metal cable tray systems, non-metallic cable tray systems, PVC insulating tape, extruded insulating tubing, heat-shrinkable tubing, crosslinked tubing, coated electrical sleeving namely, Grade A acrylic-polymer-coated electrical sleeving, Grade A silicone-polymer-coated electrical sleeving, Grade A vinyl-polymer-coated electrical sleeving, Grade B acrylic-polymer-coated electrical sleeving, Grade B silicone-polymer-coated electrical sleeving, Grade B vinyl-polymer-coated electrical sleeving, belowground reinforced thermosetting resin conduit, belowground reinforced thermosetting resin conduit fittings, aboveground reinforced thermosetting resin conduit, aboveground reinforced thermosetting resin conduit fittings, cable ties for electrical installations namely, metallic cable ties and their associated fixing devices, non-metallic cable ties and their associated fixing devices, composite cable ties and their associated fixing devices, electrical quick-connect terminals namely, connectors, tabs, splicing wire connectors namely, sealed wire connector systems namely, insulating caps, insulating covers, insulating

resins, insulating tubing, insulating tapes, insulated multi-pole splicing wire connectors namely, multi-pole non-mating splicing wire connectors, multi-pole mating splicing wire connectors, electrical resistance heating cables, electrical resistance heating device sets namely, heating cables cable sets, surface heating device sets, electrical wires, electrical cables, cord sets and power supply cords namely, cord reels, general use and hospital Grade moulded-on cord connectors, general use and hospital Grade moulded-on attachment plugs, cord-connected multiple receptacle extension boxes, low-energy control cable namely, extra-low-voltage control circuit cable, extra-low-voltage control cable, thermoset-insulated wires, thermoset-insulated cables, flexible cords and cables namely, flexible cords elevator cables, hoistway cables, service cords, elevator cables, heater cords, range cords, dryer cords, cords for decorative lighting, tinsel cords, lamp cords, special use cords, underground service-entrance cables, underground secondary cables, thermoplastic-insulated wires, thermoplastic-insulated cables, portable power cables, thermoset and pur multiconductor round cables for mining and general applications, thermoset two- and three-conductor flat cables for mining and general applications, thermoset three-conductor round cables with a central bonding (grounding) conductor for underground coal mining applications, arc-welding cable namely, single-conductor portable power cable, single conductor PPC cables for general applications, multiconductor PPC cables for general applications, flexible cable for use with cranes, flexible cable for use with hoists, variable frequency drive cable three conductor round or mining and general applications, DLO cable single conductor used for portable and general applications, mine power feeder cables, metal sheathed cables, mineral-insulated cable namely, mineral-insulated cables with copper enclosed in a copper sheath, mineral-insulated cables with nickel-/nickel-alloy-clad copper enclosed in a copper sheath, mineral-insulated cables with steel-clad copper enclosed in a copper sheath, mineral-insulated cables with nickel conductors enclosed in a copper sheath, mineral-insulated cables with copper enclosed in a stainless steel sheath-, mineral-insulated cables with nickel-/nickel-alloy-clad copper enclosed in a stainless steel sheath, mineral-insulated cables with steel-clad copper enclosed in a stainless steel sheath, mineral-insulated cables with nickel conductors enclosed in a stainless steel sheath, equipment wires namely, lead wires, insulated conductors intended for internal wiring of electrical equipment for leads of transformers motors, insulated conductors intended for internal wiring of electrical equipment for luminous-tube signs, insulated conductors intended for internal wiring of electrical equipment for ignition systems, neutral-supported cables, type TECK 90 cable namely, single- conductor Type TECK 90 armoured cable, multi-conductor Type TECK 90 armoured cable, airport series lighting cables, fire alarm cable and signal cable namely, single- conductor fire alarm cables, multiple-conductor fire alarm cables, single-conductor signal cables, multiple-conductor signal cables,

communications cables namely, single- or multiple-conductor, jacketed or unjacketed, integral or non-integral cables, and single or multiple coaxial cables for telephone and other communication circuits such as voice data and audio for on-premise customer systems, tray cables namely, single conductor constructions without metal sheath or armour suitable for use in cable trays and other applications, multi-conductor constructions without metal sheath or armour suitable for use in cable trays and other applications, optical fiber cables namely, non-conductive optical fiber cable, conductive optical fiber cable, cords for communication systems namely, cord sets for communication systems, single-conductor cord sets, single-conductor cords, paired-conductor cords, paired-conductor cord sets, multi-conductor cords, multi-conductor cord sets, control and instrumentation cables namely, multiple-conductor control cables, instrumentation cables, thermocouple cables, thermocouple extension cables, multiple-conductor thermoplastic or thermoset-insulated assemblies, shielded or unshielded, twisted or cabled, paired or grouped into units, jacketed or unjacketed, sheathed or unsheathed, armoured or unarmoured, and any combinations thereof cables, marine shipboard cable, optical fiber cable, communication cable raceway systems, metallic outlet boxes, metallic concrete boxes, metallic extension rings, metallic covers, metallic conduit bodies, metallic bar hangers, metallic bar-hanger assemblies, accessories whose principal function is for support of boxes, marine application metallic outlet boxes, marine application flush-device boxes, marine application special purpose boxes, marine application extension rings, marine application covers, metallic box extenders, non-metallic outlet boxes, non-metallic conduit concrete floor boxes, non-metallic pull boxes, non-metallic device boxes, multiple-gang boxes, extension rings, closure plugs, outlet box covers, non-metallic box extenders, electrode receptacles for gas tubes, electrode fittings for gas tubes, electrode connectors for gas tubes, electrode fittings for mounting gas tubes, electrode receptacles for mounting gas tubes, connectors that are intended to enclose the ends of gas tube electrodes and to provide a connection to the secondary voltage supply, general use receptacles attachment plugs namely, wiring devices of the general purpose nonlocking and locking types, general use attachment plugs, hospital-Grade attachment plugs, adapters without male or female screwshell, general use receptacles including those intended for use with aluminum wire and those of the self-contained type, hospital-grade receptacles including those intended for use with aluminum wire and those of the self-contained Type, general use cord connectors, hospital-grade cord connectors, current taps and similar devices such as flanged equipment power inlets and outlets, the following devices for use with copper conductor non-metallic sheathed cables for mounting without a separate outlet Box, self-contained receptacles intended for flush mounting, surface-mounted receptacles, cover plates for flush-mounted wiring devices namely, non-metallic cover plates and associated gaskets for flush-mounted wiring

devices, metallic cover plates and associated gaskets for flush-mounted wiring devices, outlet box hoods, cover plates for flush-mounted wiring devices intended for use in marine applications, appliance plugs for heater cord sets, attachment plugs receptacles namely, receptacles with attachment plugs, receptacles with attachment plugs interlocked with circuit breakers, receptacles with attachment plugs interlocked with switches, cable and cord connectors couplers and flanged equipment power inlets and flanged equipment power outlets, plugs receptacles of the pin and sleeve type, cable connectors of the pin and sleeve type, pin and sleeve type plugs, receptacles, power inlets and connectors, industrial locking type special use attachment plugs, industrial locking type special use receptacles, industrial locking type special use connectors namely, locking type plugs, locking type receptacles, locking type equipment power inlets, locking type equipment power outlets and connectors, locking type equipment power connectors, special use attachment plugs, receptacles and connectors namely, power outlets intended for use in electronic and electrical applications, plugs intended for use in electronic and electrical applications, receptacles intended for use in electronic and electrical applications, power inlets intended for use in electronic and electrical applications, power connectors intended for use in electronic and electrical applications, similar wiring devices intended for use in electronic and electrical applications, busways namely, service-entrance feeder busway, branch-circuit busways, service-entrance feeder associated fittings, branch-circuit busway associated fittings, splitters, metal-enclosed high-voltage busways, outdoor metal-enclosed busways, indoor metal-enclosed busways, straight bus sections, elbows, tees, adapter boxes, wall flanges, forced-cooled busways, nonforced-cooled busways, isolating links, expansion joints, constructions with rigid bus conductors, constructions with cable type conductors; cylinder connection devices namely, electric plug devices enabling connection and disconnection of power and/or control cables; decision logic equipment namely, central processing units for computers, EPROMs, programmable logic chips, ROMs; Decorative gas appliances namely, gas fireplaces; decorative lighting outfits namely, candle sets, chandeliers, Christmas flashers, crosses, motorized devices intended for indoor use only such as tree stands with or without provision for illumination and colour wheels, parallel-connected strings having candelabra-intermediate- or medium-base lampholders, parallel-connected strings having midget- or miniature-base lampholders supplied by a transformer, plaques, series-connected strings having midget- or miniature-base lampholders, stars, motorized or non-motorized devices intended for indoor or outdoor use such as a silhouette or sculpture with provision for illumination by means of decorative lighting outfits or a flexible light cable system (Ropelight), flexible light cable system (Ropelight), wall sconces, wreaths; bonding and grounding of electrical equipment namely, armoured grounding wires, bonding devices, bonding wires, electrical grounding adjustable

ankle bands, electrical grounding adjustable wrist bands, electrical grounding rods, electrical grounding strips flat ribbon grounding cables, equipment for making electrical connections between grounding electrodes, equipment for making electrical connections between the grounding conductors used in electrical power systems, equipment for making electrical connections between the grounding conductors used in telecommunications systems such as telephone, radio, CATV network, power broadband, ground rod connectors, ground wedges, grounding bushings, grounding electrodes, hospital grounding jacks, hospital mating grounding cord assemblies, metal raceways, non-current-carrying metal parts of electrical equipment, water-meter shunts;

(11) Combustible fuel electrical equipment namely, coils, relays, solenoids, thermostats, electrical features of fuel-burning equipment namely, combination ranges,

Certification mark text

The applicant has granted licences to use the certification mark in association with all the specific wares listed hereafter that meet the defined standard (on file), and the certification mark has been used by the licenses in Canada accordingly in association with such wares. The certification mark has been used in Canada as aforesaid in association with the general class of wares comprising the following specific wares since at least

combustion controls, cooking ranges, gas-burning appliances and equipment, gas valves, hot-water heating equipment, incinerators, industrial cleaning machines, industrial heating machines, industrial processing equipment, oil valves, oil-burning appliances and equipment, room heaters, solid fuel-burning appliances, steam-heating equipment, warm-air heating equipment, electric furnaces in combination with solid fuel-fired furnaces namely, central warm air electric resistance type furnaces; electrical equipment for use in the presence of combustible dust namely, electric machine motors for use in hazardous locations, electric generators and devices for use in hazardous locations, bone dust removers, dust collectors, enclosures for use in class ii groups e f and g hazardous locations, generators for use in hazardous locations, motors for use in hazardous locations, intrinsically safe and non-incendive equipment for use in hazardous locations, cables for use in hazardous locations, cable glands for use in hazardous locations, electrical apparatus for use in the presence of combustible dust - electrical apparatus protected by enclosures and surface temperature limitation, electric luminaires for use in hazardous locations namely, luminaires of the pendent type having fluorescent lamps, luminaires of the pendent type having incandescent lamps, luminaires of the pendent type having high-intensity discharge lamps, luminaires of the recessed type having fluorescent lamps, luminaires of the recessed type having incandescent lamps, luminaires of the recessed type having high-intensity discharge lamps, luminaires of the surface mounting type having fluorescent lamps, luminaires of the surface mounting type having incandescent lamps, luminaires of the surface mounting type having and high-intensity discharge lamps; enclosures for electrical equipment namely, electrical power distribution enclosure units, special purpose enclosures, special purpose enclosures for indoor use, special purpose enclosures for outdoor use, enclosures for electrical equipment non-environmental considerations, enclosures for electrical equipment environmental considerations, electrical equipment for explosive gas atmospheres namely, gas detectors, enclosures for use in class ii groups e f and g

<p>as early as the dates so indicated.</p>	<p>hazardous locations, generators for use in hazardous locations, motors for use in hazardous locations, intrinsically safe and non-incendive equipment for use in hazardous locations, cables for use in hazardous</p>
<p>Classification data</p>	<p>locations, cable glands for use in hazardous locations, non-incendive electrical equipment for use in class i division 2 hazardous locations, series electrical apparatus for explosive gas atmospheres, electrical apparatus for explosive gas atmospheres flameproof enclosures "d",</p>
<p>Disclaimer</p> <p>The classification data is provided for information and searching purposes only. CIPO does not warrant the accuracy of the classes assigned to the trademark. This data has no legal value of any kind.</p>	<p>electrical apparatus for explosive gas atmospheres pressurized enclosures "p", electrical apparatus for explosive gas atmospheres powder filling "q", powder-filled electrical apparatus and ex components may contain electronic circuits, transformers, protection fuses, relays, intrinsically safe electrical apparatus, associated electrical apparatus switches, etc, electrical apparatus for explosive gas atmospheres oil-immersion "o", electrical apparatus for explosive gas atmospheres increased safety "e", electrical apparatus for explosive gas atmospheres intrinsic safety "i", electrical apparatus for explosive gas atmospheres type of protection "n", electrical apparatus for explosive gas atmospheres encapsulation "m", electrical equipment for flammable and combustible fuel dispensers namely, dispensers for petroleum-based liquids, electric luminaires for use in hazardous locations namely, luminaires of the pendent type having fluorescent lamps, luminaires of the pendent type having incandescent lamps, luminaires of the pendent type having high-intensity discharge lamps, luminaires of the recessed type having fluorescent lamps, luminaires of the recessed type having incandescent lamps, luminaires of the recessed type having high-intensity discharge lamps, luminaires of the surface mounting type having fluorescent lamps, luminaires of the surface mounting type having incandescent lamps, luminaires of the surface mounting type having and high-intensity discharge lamps; explosion proof electrical equipment namely, enclosures, devices, assemblies, enclosures for use in class ii groups e f and g hazardous locations, explosion-proof enclosures for use in class i hazardous locations, generators for use in hazardous locations, motors for use in hazardous locations, intrinsically safe and non-incendive equipment for use in hazardous locations, cables for use in hazardous locations, cable glands for use in hazardous locations, electric luminaires for use in hazardous locations namely, luminaires of the pendent type having fluorescent lamps, luminaires of the pendent type having incandescent lamps. luminaires of the pendent type having high-intensity discharge lamps, luminaires of the recessed type having fluorescent lamps, luminaires of the recessed type having incandescent lamps, luminaires of the recessed type having high-intensity discharge lamps, luminaires of the surface mounting type having fluorescent lamps, luminaires of the surface mounting type having incandescent lamps, luminaires of the surface mounting type having and high-intensity discharge lamps; insect killer electrical equipment namely, insect killing lights and lamps; portable electrical equipment namely, cellular phones, centrifugal atomizing humidifiers, dehumidifiers,</p>
<p>Claims</p> <p>Used in CANADA since at least as early as November 01, 2008 on goods (10), (11)</p> <p>Used in CANADA since at least as early as 1944 on goods (1)</p> <p>Used in CANADA since at least as early as 1952 on goods (2)</p> <p>Used in CANADA since at least as early as 1954 on goods (3)</p> <p>Used in CANADA</p>	<p>having fluorescent lamps, luminaires of the recessed type having incandescent lamps, luminaires of the recessed type having high-intensity discharge lamps, luminaires of the surface mounting type having fluorescent lamps, luminaires of the surface mounting type having incandescent lamps, luminaires of the surface mounting type having and high-intensity discharge lamps; explosion proof electrical equipment namely, enclosures, devices, assemblies, enclosures for use in class ii groups e f and g hazardous locations, explosion-proof enclosures for use in class i hazardous locations, generators for use in hazardous locations, motors for use in hazardous locations, intrinsically safe and non-incendive equipment for use in hazardous locations, cables for use in hazardous locations, cable glands for use in hazardous locations, electric luminaires for use in hazardous locations namely, luminaires of the pendent type having fluorescent lamps, luminaires of the pendent type having incandescent lamps, luminaires of the pendent type having high-intensity discharge lamps, luminaires of the recessed type having fluorescent lamps, luminaires of the recessed type having incandescent lamps, luminaires of the recessed type having high-intensity discharge lamps, luminaires of the surface mounting type having fluorescent lamps, luminaires of the surface mounting type having incandescent lamps, luminaires of the surface mounting type having and high-intensity discharge lamps; insect killer electrical equipment namely, insect killing lights and lamps; portable electrical equipment namely, cellular phones, centrifugal atomizing humidifiers, dehumidifiers,</p>

<p>since at least as early as 1957 on goods (4) Used in CANADA</p> <p>since at least as early as 1958 on goods (5) Used in CANADA</p> <p>since at least as early as 1961 on goods (6) Used in CANADA</p> <p>since at least as early as 1962 on goods (7) Used in CANADA</p> <p>since at least as early as 2000 on goods (8) Used in CANADA</p> <p>since at least as early as August 2008 on goods (9)</p>	<p>desk fans, electric fans, electronically commutated (brushless) dc component fans, evaporative-media humidifiers, fan-type air-to-air heat exchangers, hand tools, hassock fans, humidifiers, pedestal fans, personal digital assistant devices, steam humidifiers, suitcase fans, utility fans, ventilators, water-injection humidifiers, motor-operated gardening appliances namely, cord-connected and battery- operated lawn mowers of the reel walking type, cord-connected and battery- operated lawn mowers of the rotary walking type, hedge trimmers, edgers, trimmers, edger trimmers, grass shears, cultivators, shredder baggers, gardening appliances with a blower leaf blower/vacuums, snow movers, chain saws, similar equipment including electric starter motors for gardening appliances; safety electrical equipment namely, air analyzer, air monitor, armored cable and connectors, carbon monoxide detectors and generators, fire protective signalling cable, fire resistive cables, gas fume alarm detectors and generators, radio telephones, smoke detectors and generators, turbo air sterilizers, electrically operated valves namely, general-purpose valves, safety valves, valves intended to be incorporated into equipment, electrically powered mechanisms that are designed to provide the signals needed for monitoring valve operation from a remote location, electrically powered valve actuators; ultraviolet electrical equipment namely, ultraviolet lights, ultraviolet radiation (UV) water treatment systems units and replaceable UV lamps intended to reduce active microorganisms in potable or contaminated water, ultraviolet lamps for purification purposes, ultraviolet lamps for sterilization purposes for use in spas hot tubs and hydrotherapy tubs, water purifiers, air purifiers, ozonators; electrical measurement and test equipment components and kits namely, ac power supplies, AC/DC current clamps, air interface monitoring, analog support rack, analogue scope, antenna cable test systems, array structure parametric test systems, automotive electronic test system, board test system, broadband light source, built-in spectral stripreader, calibration meters, capacitance meters, carrier noise amplifier, cellular phone test system, chromatic test set /system, circuit analyzers, clamp-on harmonic meters, colour measurement systems, component analyzers, conductivity meters, control switch, copper loop testers, current 7 temperature controllers for laser diodes, current meters, data logggers, data timing generators, dc power supplies, digital audio monitor, digital scope, distributed network analyzers, dual block calibrators, endoscopy quality test systems, Erbium doped fiber amplifiers, frequency counters, frequency divider, grounding tester, handheld cable fault finder, handheld digital thermometers, handheld telephone line testers, harmonic meters, HDTV parallel-serial converters, HDTV waveform monitor, high power curve tracers, high voltage probes, hipot testers, image processor system, internet adviser protocol analyzers, isolation units, LAN and WAN probes, LCR meters, leakage low current, light source solutions, lightwave measurement system, logic analyzers, logic and modulation analyzers, mainframes for test equipment,</p>
---	---

measurement system solutions, motor performance tracker, MPEG generator, arbitrary functional generators, multi-channel fiberoptic signal conditioner, multifunction calibrators, multimeters data acquisition, multimeters, multi-port test set, network analyzers, optical lightwave multimeter, optical power meters, optical sampler, optical thickness gauge, oscilloscope calibrators, parametric test systems, passive optical instrument, performance modeling system, phase noise test systems, photonics test systems, PNA network analyzers, power measurement, pressure calibrators, process calibrators, programmable curve tracer, pulse generators, pulse data generator, realtime spectrum analyzers, reflectrometers, RF systems, RMU interface panel, scopemeters, semiconductor device analyzer, serial bit error rate testers, solar array simulators, spectrum analyzer, switch matrixes, sync pulse generators, T1/E1 and DS3/E3 WAN analyzer, temperature calibrators, transducers, transmission Tunable sources, up/down converter, video measurement sets, vision metrology inspection system, voice quality testers, voltmeters, VXI tuners, waveform generators, wireless appliance function tester, wTV generator platform, x-ray scanner; electrical tools namely, band saws, bank saws, belt sanders, blowers, circular saws, clutch screwdriver, combination lathe, combination mixer-grinders, compass saws, concrete vibrators, cut-off machines, cutters, depth sensitive screw gun, desoldering devices, diamond core drills, disc lathe, disk-type sanders, drain cleaners, drywall screw gun, drill bit sharpeners, drills, drill-screw driver combinations, electric brad nail gun kit, electric chain saws, glue guns, grass shears, grass trimmers, grinders, grinding machines, hammer drill, hammers, hand circular, hand motor tools, hand-held magnetically operated staplers, heat blowers, impact drills, impact wrenches, jigsaws, jointers, jointers for cutting into wood, magnetic drill presses, nibblers, orbital polishers, orbital sanders, paint-scraping tools, pattern saw, planers, polishers, precision tools, random orbit polishers, random orbit sanders, reciprocating polishers, reciprocating sanders, reciprocating saws, rotary hammers, routers, sabre saws, sanders, sanders and polishers other than disk type, saws, screwdrivers, scudrill, sealing irons, shears, shrub trimmers, soldering guns, soldering irons of the resistance and the transformer type, solder-pot tips, staplers, strapping Tools, swivel head shear, tackers, tappers, tire regroovers, transportable motor-operated electric tools namely, trimmers, vacuum cleaners, vibration chisels, welding machines, wood-burning tools, arc welding equipment namely, single-phase transformers, single-phase transformer-rectifiers, polyphase-transformers, polyphase-transformer-rectifiers, motor-driven alternators, motor-driven generators, engine-driven alternators, engine-driven generators, electrical attachments such as wire drive units, arc stabilizer units, remote controls and optional kits; plasma arc equipment, electrical equipment for woodworking machinery namely, ac and dc type power supplies including rack-mounted and modular units that are of dry or liquid-filled construction; have a rated voltage

not exceeding 600 V; and are for commercial industrial and residential indoor and outdoor use, industrial dc power supplies, power converters for recreational vehicles, static transfer switches, inverters, uninterruptible ac power supplies (UPS), telecommunication equipment power supplies, CATV power supplies, power conversion equipment for use in utility-interconnected inverters, dc charge controllers, electric vehicle chargers; flammable liquid handling equipment namely accessories namely, portable gas cans, portable marine gas cans, portable marine fuel tanks, portable metal petroleum fuels containers, portable plastic petroleum fuels containers; digester gas fuel burning equipment namely, combustion chambers tanks and gas holders; gaseous fuel burning equipment namely, combustion chambers tanks and holders; kerosene fuel burning equipment namely, combustion chambers tanks and holders; landfill gas fuel burning equipment namely, combustion chambers tanks and holders; liquefied petroleum fuel burning equipment namely, combustion chambers tanks and holders; oil fuel burning equipment namely, combustion chambers tanks and holders; natural gas fuel burning equipment namely, combustion chambers tanks and holders; nozzles for fuel burning equipment namely, metal nozzles, fuel burning nozzles; vaporizing-type fuel burning equipment namely, vaporizing potsair supply devices; fuel station equipment namely, cardlock motor fuel pumps, service station tank vents, fill and vapour caps, drain pockets, paper towels, hand cleaners, motors for use in hazardous locations, generators for use in hazardous locations, combustible gas detection instruments, intrinsically safe and non-incendive equipment for use in hazardous locations, cables for use in hazardous locations, cable glands for use in hazardous locations, non-incendive electrical equipment for use in class i division 2 hazardous locations, electrical apparatus for use in the presence of combustible dust - electrical apparatus protected by enclosures and surface temperature limitation, petroleum and flammable liquid containers and equipment namely, aboveground flammable liquid tanks, fittings pigtails and flexible hose connectors, flammable liquid containers, inside tanks for oil burner fuel, LP-gas check valves electrically operated valves, LP-gas hose assemblies, LP-gas hose, LP-gas power-operated pumps, LP-gas regulators shut-off valves electrical insulation bushing fuel filters, non-metallic petroleum product containers, portable marine fuel tanks, underground flammable liquid tanks, electrical equipment for flammable and combustible fuel dispensers namely, dispensers for petroleum-based liquids, enclosures for use in class ii groups e f and g hazardous locations, explosion-proof enclosures for use in class i hazardous locations, electric luminaires for use in hazardous locations namely, luminaires of the pendent type having fluorescent lamps, luminaires of the pendent type having incandescent lamps, luminaires of the pendent type having high-intensity discharge lamps, luminaires of the recessed type having fluorescent lamps, luminaires of the recessed type having incandescent lamps, luminaires of the recessed type having high-intensity discharge lamps, luminaires of

the surface mounting type having fluorescent lamps, luminaires of the surface mounting type having incandescent lamps, luminaires of the surface mounting type having and high-intensity discharge lamps, series electrical apparatus for explosive gas atmospheres namely, electrical apparatus for explosive gas atmospheres flameproof enclosures "d", electrical apparatus for explosive gas atmospheres pressurized enclosures "p", electrical apparatus for explosive gas atmospheres powder filling "q", powder-filled electrical apparatus and ex components may contain electronic circuits, transformers, protection fuses, relays, intrinsically safe electrical apparatus, associated electrical apparatus switches, etc, electrical apparatus for explosive gas atmospheres oil-immersion "o", electrical apparatus for explosive gas atmospheres increased safety "e", electrical apparatus for explosive gas atmospheres intrinsic safety "i", electrical apparatus for explosive gas atmospheres type of protection "n", electrical apparatus for explosive gas atmospheres encapsulation "m"; furniture namely, bedroom furniture, benches, cabinets, computer furniture, dining room furniture, drapery, living room furniture, modular wiring systems for office furniture, office furniture, outdoor furniture, patio furniture, television carts, television ceiling mount, television ceiling mounting brackets, television ceiling mounts, television desk swivel stands, television stands, television table mounts, television wall brackets, television wall mounts; graphic arts equipment namely, 35mm accessories, cameras, color video display terminals, computer printers, electronic and laser plotters and cameras, electronic keyboards and control consoles, ink jet printers, motion picture projectors, optical scanners, overhead projectors, personal image processors, photo contrast kits, photographic developing and reproduction equipment, photographic enlargers, photo reproduction appliances, projectors and similar appliances; amusement and personal services appliances namely, amusement machines, arcade games, automatic bowling alley scoring systems, bill acceptor retrofit kit, billiard tables, black jack machines, bowling machines, card re-value machines, coin operated game devices, computer games, currency dispensers, dartboards, driving simulators, electric arm wrestle machines, electromechanical games, electronic dart games, electronic game equipment for playing video games, electronic promotion system for casino game, gaming machines, joystick control box, kiddie rides, laser shooting appliances, lottery slant top terminals, luggage lockers, miniature bowling game equipment, personal service machines, pin ball machines, roulette games, server for slot machines, shoe shining appliances, slant top slot machines, slot machine, touch-screen control box, upright slot machines, video game machines, video games, video lottery, weighing machines; battery operated appliances namely, battery operated coffee makers, battery operated blenders, battery operated refrigerators; bains-marie namely, water bath heaters, storage-tank water heaters namely, permanently connected storage-tank water heaters, electric sauna heating equipment namely, sauna heater unit intended for fixed installation in

a special room that is built or assembled in the field to conform to the manufacturer's size specifications, combination of a sauna heater or heater units and a prefabricated factory-built room or cabinet in which the assembled combination may be specified for field installation or that may be supplied with a power supply cord and intended to be fastened in place or located in a dedicated space; coffee product appliances namely, coffee bean roasters, coffee grinders, coffee grinding and coffee milling attachments, coffee makers, coffee mills, coffee stoves, dispensing units for coffee beans; disposal appliances namely, waste disposal bins, waste receptacles, household trash compactors, food-waste disposers, commercial waste shredder/compactor; electrical hot cupboards for domestic and industrial use; motor operated appliances namely, appliances provided with a worm conveyor such as mincers, noodle attachments, and berry juice extractors, automotive equipment analyzers, automotive servicing equipment, baby-food grinders and choppers, baby-food warmers /servers, barbecue motors, beds, blenders for food, blenders for liquids, broilers, can openers, car wash equipment, centrifugal juicers for fruit and vegetables, chairs, cheese graters, churns, citrus fruit juice squeezers, cord-connected appliances for household and commercial use, cream whippers, egg beaters, egg boilers, engine timing lights, exercise appliances, feeding-bottle heaters, food processors, food-waste disposers, freezers, graters and shredding appliances for vegetables and fruits, hair clippers, hand-held engravers, hot pots, household trash compactors, ice crushers, ice-cream appliances including bucket Type and those for use in refrigerators, knife sharpeners, knives, laundry appliances, milk heaters, mixers, outdoor electric barbecues, outdoor electric grills, paint rollers, paint sprayers, parts cleaners, pasta mixer-extruders, permanently connected appliances for household and commercial use, portable ovens, potato peelers, pressure cookers, radiant grills, rice cookers, roasters, rotary grills, rotisseries, sewing machines, sieving appliances, slicing appliances for beans, slicing appliances for bread, cheese, meat, and the like, slow cookers, small electric kitchen appliances, sprayers intended for extensive open spraying of cleaning fluids, paint, insecticides and similar liquids, toaster oven, toasters, vacuum cleaners, vegetable steamers, wheel aligners, yoghurt-makers; portable cooking appliances namely, electric or gas portable domestic cooking devices, baby-food warmers/servers, egg boilers, feeding-bottle heaters, hot pots, milk heaters, outdoor electric barbecues /grills, portable ovens, pressure cookers, radiant grills, rice cookers, roasters, rotary grills, rotisseries, slow cookers, toaster oven/broilers, toasters, vegetable steamers, yoghurt-makers; skin or hair care appliances namely, curling combs, curling irons, curling rollers with separate heaters, dry shavers, facial saunas, hair brushes, hair clippers, hair crimping irons, hair curlers, hair cutting equipment, hair cutting scissors, hair dryers, hair rollers, hair straighteners, hand dryers, heaters with detachable curlers, irons, permanent-wave appliances, shaver

accessories, skin care hygiene appliances namely personal massaging and cleansing appliance for use on the human face, spas hot tubs and associated equipment, shavers hair clippers and similar appliances namely, appliances used for manicure and pedicure, appliances for hairdressers, hairdressing equipment namely, household and commercial electrical hairdressing equipment of the portable pedestal and table-mounted types and the attachments with which they are sold, hair dryers and the attachments with which they are sold, hair steamers and the attachments with which they are sold, combs and the attachments with which they are sold, curlers and the attachments with which they are sold; laser equipment namely, blue ray writer/ readers, CD writer/readers, DVD writer/readers, fiber optic modules, laser communication modules, laser disk players, laser measuring systems, laser scanners, lasers for medical and non-medical use; motorized components for hygiene and cosmetic appliances namely, motorized components for electrical tooth brushes, oral irrigators, hair clippers, hairdressing equipment namely, household and commercial electrical hairdressing equipment of the portable pedestal and table-mounted types and the attachments with which they are sold, hair dryers and the attachments with which they are sold, hair steamers and the attachments with which they are sold, combs and the attachments with which they are sold, curlers and the attachments with which they are sold, massage appliances namely, hand-held massagers, foot massagers, massage belts, massage pads, massage chairs, massage beds, shavers hair clippers and similar appliances namely, appliances used for manicure and pedicure, appliances for hairdressers, dry shavers, shaver accessories, hair clippers; skin care, hygiene and cosmetic appliances, cosmetic appliances namely, hair brushes, hair crimping equipment, hair curlers, hair cutting equipment, hair cutting scissors, hair dryers, hair rollers, hair straighteners, irons, skin care hygiene appliances namely personal massaging and cleansing appliance for use on the human face, radiant heaters for cosmetic or hygienic purposes in nonmedical applications, infrared lamp assemblies for cosmetic or hygienic purposes in nonmedical applications, ultraviolet lamp assemblies for cosmetic or hygienic purposes in nonmedical applications, hairdressing equipment namely, household and commercial electrical hairdressing equipment of the portable pedestal and table-mounted types and the attachments with which they are sold, hair dryers and the attachments with which they are sold, hair steamers and the attachments with which they are sold, combs and the attachments with which they are sold, curlers and the attachments with which they are sold, oral hygiene appliances namely, tooth brushes, oral irrigators, massage appliances namely, hand-held massagers, foot massagers, massage belts, massage pads, massage chairs, massage beds; protective devices namely, knee, chest, back, shoulder and elbow protectors and pads, safety bars, guards and shields, hearing protective devices namely active noise reduction ear muffs, protective devices for electric circuits and electrical

apparatus namely, electric fuses, lightning arresters, electric fountains; kitchen utensils namely, basting brushes, basting syringes, bench scraper, blender, bone scissors, bread knives, browning trays, candy thermometers, can openers, casseroles, cauldrons, cheese cloths, cheese graters, cheese slicers, chef's knives, chop sticks, colanders, cookie cutters, corkscrews, crockery, cutting boards, egg piercers, egg slicers, fillet knives, fish slices, frying pans, garlic presses, graters, grills, kitchen scissors, knives, knife grinders, ladles, lemon squeezers, lemon zesters, mated colander pots, measuring cups, measuring spoons, meat knives, meat thermometers, mixing bowls, mixing spoons, mortars, muffin tins, nut crackers, oven mitts, pastry bags, pastry brushes, peelers, pepper mills, pestles, pizza cutters, potato mashers, potato peelers, potato ricers, potholders, puree sieves, rolling pins, roulade needles, salamanders, salamander grills, salt shakers, saucepans, scales, scoops, sieves, skillets, slotted spoons, spatulas, spiders, strainers, timers, tinfoil, tongs, tomato knives, vegetable knives, whisks, wooden spoons; manufacturing plants namely, precast concrete manufacturing plants, structural glue-laminated timber manufacturing; communication medical electrical equipment namely, gas monitoring units, nurse-patient signalling and communication systems essentially comprised of a master nurse station communication unit a bedside calling station and a corridor signal light separately or as a unit annunciators, power supplies for nurse call systems; pressurized equipment namely, gas cylinders of metal for the storage of pressurized gas, pressurized lines and engine systems for propane consuming vehicles, pressurized sprayers for the application of insecticides, permanently connected and cord-connected appliances for household and commercial use, automotive servicing equipment, car wash equipment, paint sprayers, parts cleaners, household trash compactors, food-waste disposers, sprayers intended for extensive open spraying of cleaning fluids paint insecticides and similar liquids; radiation emitting equipment and accessories namely, radiation detectors, radiation shields, non-medical x-ray inspection instruments for use in the field of chemical, biochemical, pharmaceutical and food processing industry; equipment for recreational vehicles namely, bathtubs, fill valves bath and shower mixing valves pressure and gravity cold water storage, fittings, kitchen faucets, lavatories, lavatory faucets, shower stalls and pans, sinks, waste assemblies, waste holding and waste water tanks, water closets, recreational vehicles certification covers the safety, vehicular, gas, plumbing and electrical features, devices for the venting of building spaces, [for installation on vertical surfaces for installation on sloping surfaces for installation on ridges for installation on horizontal surfaces; and for installation on soffits on the underside of eaves or overhangs]; solid fuel burning equipment namely, furnaces, boilers, stoves, fireplaces, water heaters; outlet boxes namely, metallic box extenders, non-metallic box extenders, metallic concrete boxes, non-metallic concrete boxes, conduit bodies, metallic covers, non-metallic

covers, metallic extension rings, non metallic extension rings, metallic floor boxes, non-metallic floor boxes, floor nozzles, flush-device boxes, junction boxes, metallic boxes known to the trade as "outlet boxes" and "conduit boxes", non-metallic boxes known to the trade as "outlet boxes" and "conduit boxes", metallic cutout boxes, non-metallic cutout boxes, non-metallic pull boxes, metallic pull boxes, flexible metal conduit, plastic underground rigid non-metallic conduit, various fittings for use with outlet boxes namely, closure plugs, strain relief bushings, bar hangers, box supports, pulling grips, metallic bar-hanger assemblies, metallic outlet boxes namely, accessories whose principal function is for support of boxes, marine application metallic outlet boxes, marine application flush-device boxes, marine application special purpose boxes, marine application extension rings, marine application covers, non-metallic outlet boxes namely, non-metallic device boxes, multiple-gang boxes; electrical metallic tubing namely, aluminum couplings, aluminum elbows, aluminum nipples, bends fabricated from mild steel, aluminum alloy or copper alloy for use with electrical metallic tubing, cable fittings, conduit bodies, conduit bodies for rigid polyvinyl chloride (PVC) conduit, conduit bushings, conduit locknuts, conduit tubing, elbows fabricated from mild steel, aluminum alloy or copper alloy for use with electrical metallic tubing, electrical metallic (aluminum) elbows, electrical metallic (aluminum) tubing, electrical metallic (steel) elbows, electrical metallic (steel) tubing, electrical metallic tubing fabricated from aluminum alloy, electrical metallic tubing fabricated from copper alloy, electrical metallic tubing fabricated from mild steel alloy, electrical metallic tubing fabricated from mild steel, aluminum alloy or copper alloy, electrical rigid metal (aluminum) conduit, electrical rigid metal (red brass) conduit, electrical rigid metal (stainless steel) conduit, electrical rigid metal conduit, electrical rigid metal conduit-steel, entrance elbows, fittings for tray cable, fittings for aluminum-sheathed cable, fittings for armored cable, fittings for electrical metallic tubing, fittings for flexible cord, fittings for flexible metal conduit, fittings for flexible metallic tubing, fittings for flexible non-metallic tubing, fittings for insulating bushings grips reducing nipples, fittings for insulating bushings grips reducing washers, fittings for intermediate metal conduit, fittings for liquid-tight flexible conduit, fittings for metal-clad cable, fittings for mineral-insulated cable, fittings for rigid metal conduit, fittings for service-entrance cable and, fittings for service-entrance heads, flexible liquid-tight non-metallic conduit metal raceway for the installation of conductors (layered integral or corrugated), flexible metal conduit, halogen-free reinforced thermosetting resin conduit (RTRC), halogen-free reinforced thermosetting resin elbows, bends and couplings, hangers staples straps, hardware for the support of cable, hardware for the support of conduit tubing, liquid-tight flexible metal conduit, liquid-tight flexible metal conduit, metal stud bushings, nipples, elbows and bends fabricated from steel aluminum stainless steel or red brass, red brass (ERMC-RB) and couplings, red brass (ERMC-RB) elbows, red brass (ERMC-RB) nipples, rigid

conduit fabricated from steel, aluminum, stainless steel or red brass couplings, rigid metal conduit, stainless steel couplings, stainless steel elbows, stainless steel nipples, steel couplings, steel elbows, steel nipples, submersible fittings; non-metallic sheathed cable namely, PVC or nylon insulated power conductors, non-metallic sheathed cable and connectors, non-metallic conduit elbows bends, non-metallic conduit bends, non-metallic conduit associated fittings, rigid types db2/es2 pvc conduit, rigid types eb1 pvc conduit, rigid PVC (unplasticized) conduit bends, rigid PVC (unplasticized) conduit elbows, rigid PVC (unplasticized) conduit couplings, type FCC under-carpet wiring system, electrical non-metallic tubing, electrical non-metallic tubing mechanically-attached fittings, liquid-tight flexible non-metallic conduit, non-metallic mechanical protection tubing; supplementary protectors namely, circuit-protection devices, enclosed switches, dead-front switches, molded-case switches, fused molded-case switches, test limiters, fuseholder assemblies namely, rejectors for Type C fuses, adapters for Type S fuses, plug fuses, cartridge fuses, HRC fuses, current-carrying parts pertaining thereto and mounted on bases of suitable insulating material, supplementary protectors namely, overcurrent-trip protectors, overvoltage-trip protectors, undervoltage-trip protectors, relay-trip protectors, accessory devices such as alarm and auxiliary switches that are installed in or on the protector to perform an auxiliary function, single- and multi-pole protectors, protectors capable of interrupting short-circuit currents, protectors not capable of interrupting short-circuit currents, series low voltage fuses namely, Class C Fuses, Class CA and CB Fuses, Class CC Fuses, Class G Fuses, Class H Non-Renewable Fuses, Class H Renewable Fuses, Class J Fuses, Class K Fuses, Class L Fuses, Plug Fuses, Class R fuses, semiconductor fuses, supplemental fuses, Class T Fuses, series fuseholders namely, fuseholders and devices accommodate fuses to be employed in electrical circuits, fuseholder accessories such as covers indicators adapters, fuseholders intended for use with Class CC Fuses, fuseholders intended for use with Class G Fuses, fuseholders intended for use with Class H Fuses, fuseholders intended for use with Class J Fuses, fuseholders intended for use with Class K Fuses, fuseholders intended for use with Type C (Edison-base) Fuses, fuseholders intended for use with Type S Plug Fuses, devices intended to be added to Edison-base fuseholders to reject fuses with larger ampere ratings, devices intended to adapt Type S plug fuses for use in Edison-base fuseholders, fuseholders intended for use with Class R Fuses, fuseholders intended for use with Class T Fuses; temperature, indicating and regulating accessories for air heaters namely, air heater hose fittings, air heater hoses, automatic electrical controls for household and similar use, electrically operated door locks, electrically operated water valves, electromagnetic interference (emi) filters, fixed capacitors for use in electronic equipment, series fixed capacitors for use in electronic equipment, temperature sensors thermal cutouts, thermal motor protectors, thermal motor

protectors for motor-compressors of hermetic and semi-hermetic type motor-compressors, thermal protectors for ballasts for tubular fluorescent lamps, timers, automatic electrical pressure sensing controls including mechanical requirements, thermal cut-offs/thermal links namely, thermal cut-offs for the protection electric motors, thermal cut-offs for the protection of transformers, thermal cut-offs for the protection fluorescent lighting ballasts, thermal cut-offs for the protection of electric heating appliances, Single operating devices (SOD), fixed capacitors for electromagnetic interference suppression and connection to the supply mains namely, capacitors and resistor-capacitor combinations which will be connected to an ac mains or other supply, automatic electrical burner control systems namely, automatic electrical burner control systems for the automatic control of burners for oil, gas, coal or other combustibles for household and similar use including heating air conditioning and similar use, Solid state oil ignitors, time switches namely, timers and time switches for household and similar use that may use electricity, gas, oil, solid fuel, solar thermal energy etc. or a combination thereof including heating air conditioning and similar applications, temperature sensing controls namely, boiler thermostats, fan controls, temperature limiters, thermal cut-outs, electrically operated motor starting relays namely, starting relays incorporating electronic devices, starting relays using thermistor elements, starting relays using thermal elements, starting relays using magnetic elements, energy regulators namely, energy regulators for heating, energy regulators for air conditioning, manual energy regulators when such are electrically and/or mechanically integral with automatic controls, energy regulators may be thermally mechanically or electrically operated, gaming machines, NTC thermistors, PTC thermistors, optoisolators, surge protective devices, varistors; laser equipment; medical electrical equipment, namely radiation products in diagnostic X-ray, programmable electrical medical systems, usability, alarms, physiologic closed-loop controllers, electron accelerators, high frequency surgical equipment, short-wave therapy equipment, cardiac defibrillators and cardiac defibrillator-monitors, ultrasonic physiotherapy, microwave therapy, high voltage generators of diagnostic X-ray, therapeutic X-ray equipment operating in the range 10kv to 1mv, patient contact dosimeters used in radiotherapy with electrically connected radiation detectors, nerve and muscle stimulators, gamma beam therapy equipment, lung ventilators for medical use, anaesthetic systems, haemodialysis, haemodiafiltration and haemofiltration equipment, remote-controlled automatically-driven gamma-ray after loading equipment, endoscopic equipment, baby incubators, transport incubators, infant radiant warmers adopted, diagnostic and therapeutic laser equipment, transcutaneous partial pressure monitoring equipment, infusion pumps and controllers, electrocardiographs, electroencephalographs, electrocardiographic monitoring equipment, X-ray source assemblies and X-ray tube assemblies for medical diagnosis, radiotherapy simulators, automatic cycling indirect blood pressure monitoring

equipment, external cardiac pacemakers with internal power source, associated equipment of X-ray equipment, magnetic resonance equipment for medical diagnosis, invasive blood pressure monitoring equipment, extracorporeally induced lithotripsy, ultrasonic medical diagnostic and monitoring equipment, electrically operated hospital beds, peritoneal dialysis equipment, electromyographs and evoked response equipment, surgical luminaires and luminaires for diagnosis, X-ray equipment for interventional procedures, X-ray equipment for computed tomography, mammographic X-ray equipment and mammographic stereotactic devices, operating tables, ambulatory electrocardiographic systems, multifunction patient monitoring equipment, infant phototherapy equipment, recording and analyzing single and multi-channel electrocardiographs, hoist for the transfer of disabled persons

- 1 - Chemicals and adhesives
- 2 - Paints, varnishes and lacquers
- 3 - Bleaching, cleaning preparations and non-medicated cosmetics
- 4 - Industrial oils, greases and fuels
- 5 - Pharmaceuticals and herbicides
- 6 - Common metals
- 7 - Machinery
- 8 - Hand tools
- 9 - Electrical, scientific and teaching apparatus and software
- 10 - Medical and veterinary devices
- 11 - Environmental control items
- 12 - Vehicles
- 14 - Precious and semi-precious metals, and jewellery
- 15 - Musical instruments
- 16 - Paper and printed goods
- 17 - Rubber and rubber goods
- 18 - Leather and artificial leather goods
- 19 - Non-metallic building materials
- 20 - Furniture, mirrors, articles not included in other classes
- 21 - Household goods and glass
- 22 - Ropes and fibres
- 24 - Textiles and textile goods
- 25 - Clothing, footwear, headgear
- 26 - Sewing and decorative items including slide fasteners
- 28 - Games, toys and playthings, sporting articles

Action History

Action	Action date	Due date	Comments
Filed	2008-11-10		
Created	2008-11-19		
Formalized	2008-11-24		
Search Recorded	2009-11-09		
Examiner's First Report	2009-11-09	2010-05-09	
Extension of Time	2010-05-19	2010-11-09	Request Letter Date: 2010 /04/30

Correspondence Created	2011-01-31	2011-07-31	
Approval Notice Sent	2011-05-05	2011-06-02	Approval notice declared void on 2011/07/22
Approved	2011-06-23		APPROVED BY PROGRAM EX200M1
Advertised	2011-07-13		Vol.58 Issue 2959
Advertisement Removed	2011-07-22		
Approval Removed	2011-07-22		
Note to file	2011-07-22		The publication is hereby declared a nullity / La publication est déclarée être une nullité
Correspondence Created	2011-11-02	2012-05-02	
Approval Notice Sent	2012-01-18	2012-02-15	
Approved	2012-03-08		APPROVED BY PROGRAM EX200M1
Advertised	2012-03-28		Vol.59 Issue 2996
Allowed	2012-07-13		
Allowance Notice Sent	2012-07-13	2013-01-13	
Registered	2012-08-24	2027-08-24	
Rep for Service Name Changed	2016-02-25		
Agent Changed	2021-04-08		From: 32 To: 3927 / Voir Preuve au dossier/See evidence on File No. 1418750